

PHILIPS

Filament Candle Clear
40W B35 E14 x3

LED

2700K

470 lm

15000 h



8718699718411



Experience warm white LED light

This Philips LED light bulb provides a beautiful, extra-warm light, an exceptionally long life and immediate, significant energy savings. With its flame colour temperature, this light bulb is the perfect choice for a cosy atmosphere.

High-quality light

- Designed for the comfort of your eyes

Choose for a sustainable solution

- Saves up to 90% Energy

Light beyond illumination

- Vintage style, modern LED technology

Highlights

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up

your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Saves up to 90% Energy



Enjoy the energy saving of LEDs without sacrificing light quality. Instantly save over 90% in energy by replacing your existing incandescent or halogen lamps

Vintage-style, modern LED

LED Classic bulbs are based on standard LED energy-saving technology. Now you can enjoy a retro-style bulb with state-of-the-art technology combined with vintage design.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional candle
- Socket: E14
- Lamp Finish: Clear
- Dimmable: No
- Bulb material: Glass

Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- LED integrated: Yes

Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 470 lm
- Warm-up time to 60% light: 0.5
- Luminous efficacy (rated) (nom.): 109

Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort

Packaging information

- EAN: 8718699718411
- EOC: 871869971841100
- Product title: LED classic 40W B35 E14 WW CL ND 3CT/4

Power consumption

- Power factor: 0.41
- Voltage: 220-240 V
- Wattage equivalent: 40
- Energy efficiency label (EEL): F
- Power: 4.3
- Energy consumption kWh/1,000 hours: 5

Product dimensions and weight

- Overall height: 97 mm
- Overall length: 97 mm
- Overall width: 35 mm

Technical specifications

- Frequency: 50-60
- Bulb technology: LED
- EPREL Registration Number: 387402

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 8718699718411
- Net weight: 0.05 kg
- Gross weight: 0.08 kg
- Height: 11.1 cm
- Length: 4.6 cm
- Width: 13 cm



Issue date: 2026-05-21
Version: 0.255

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com