

# PHILIPS

Filament Candle  
Clear 40W P45 E27

LED

2700K

470 lm

15000 h



8718699763176



## Warm white light, no compromise on light quality

Familiar shapes you know and love. They use around 85% less energy than traditional light bulbs thanks to the latest LED energy-saving technology, and last ten times longer.

### Choose a simple replacement for your old lamps

- Similar shape and size as standard incandescent bulbs

### Create the right light for your home

- Perfect for decorative fixtures

### High-quality LED light that lasts for decades

- Designed for the comfort of your eyes

# Highlights

## Replaces standard incandescents



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, energy-saving standard LED bulb. The perfect sustainable replacement for traditional standard incandescent bulbs.

## Perfect for decorative fixtures



Contemporary lighting in Philips LED lustres for use in decorative fixtures such as chandeliers, ceiling fans, vanity strips and post lights.

## Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional lustre
- Socket: E27
- Lamp Finish: Clear
- Dimmable: No
- Bulb material: Glass

## Lamp dimensions

- Height: 8 cm
- Width: 4.5 cm

## Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000 h

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 470 lm
- Warm-up time to 60% light: Instant full light
- Colour Code: 827 | CCT of 2700K

## Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort

## Other characteristics

- Efficacy: 109 lm/W

## Packaging information

- EAN: 8718699763176
- EOC: 871869976317600
- Product title: LED classic 40W E27 WW P45 CL ND RFSRT4

## Power consumption

- Power factor: 0.41
- Voltage: 220-240 V
- Wattage: 4.3 W
- Wattage equivalent: 40 W
- Energy efficiency label (EEL): F

**Product dimensions and weight**

- Length: 8 cm

**Technical specifications**

- Frequency: 50-60 Hz
- EPREL Registration Number: 387410

**Packaging dimensions and weight**

- EAN/UPC - product: 8718699763176
- Net weight: 0.02 kg
- Gross weight: 0.04 kg
- Height: 12.7 cm
- Length: 5.3 cm
- Width: 6.3 cm



Issue date: 2025-04-19  
Version: 0.480

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)