

PHILIPS

Filament Bulb Frosted
200W A95 E27

LED

4000K

3452 lm

15000 h



8718699764654



Bright LED lighting with excellent light quality

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

High-quality light

- Designed for the comfort of your eyes

Choose for a sustainable solution

- Long-life bulbs – Last up to 15 years

Light beyond illumination

- A simple LED for everyday use

Highlights

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

A simple LED for everyday use



The Philips everyday LED is the perfect lamp for your basic lighting needs. It provides the beautiful light and dependable performance that you expect from LED at an affordable price.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional bulb
- Socket: E27
- Dimmable: No
- Lamp Finish: Frosted
- Bulb material: Glass

Durability

- Number of switch cycles: 20,000
- Ambient temperature range: -20 to +45 °C
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Guarantee

- Warranty period: 2 years

Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 4000 K
- Nominal luminous flux: 3452 lm
- Warm-up time to 60% light: 0.5 s
- Colour Code: 840 | CCT of 4000K
- Correlated Colour Temperature (Nom): 4000 K
- Luminous Flux: 3,452 lm
- Stroboscopic effect: 0.4
- Luminous efficacy (rated) (nom.): 150.00 lm/W

Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort

Other characteristics

- EU RoHS compliant: Yes

Packaging information

- EAN: 8718699764654
- EOC: 871869976465400
- Product title: LED classic 200W A95 E27 CW FR ND 1PF/4

Power

- Power Factor (Fraction): 0.51

Power consumption

- Power factor: 0.51
- Voltage: 220–240 V
- Wattage equivalent: 200 W
- Energy efficiency label (EEL): D
- Power: 23 W
- Energy consumption kWh/1,000 hours: 23

Product dimensions and weight

- Overall height: 165 mm
- Overall length: 165 mm
- Overall width: 95 mm

Rated values

- Rated lifetime: 15,000

Technical specifications

- Frequency: 50–60
- Diameter: 95 mm
- EPREL Registration Number: 374909
- Flux measurement reference: Sphere
- Dimmable: No
- Flickering value (PstLM): 1
- Line Frequency: 50 to 60
- Cap base: E27
- Can it be used in closed luminaires: No

Packaging dimensions and weight

- EAN/UPC - product: 8718699764654
- Net weight: 0.1 kg
- Gross weight: 0.16 kg
- Height: 22.6 cm
- Length: 10.2 cm
- Width: 13 cm



Issue date: 2025-12-31
Version: 0.310

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com