

PHILIPS

Bulb 60 W A60 B22
x3

LED

2700K

806 lm

15000 h



8718699775469



Bright LED lighting

Philips LED light bulbs provide high-quality light, an exceptionally long life and immediate, significant energy savings.

High-quality light

- Learn about light

Choose a simple replacement for your old lamps

- Similar shape and size as standard incandescent bulbs

Choose for a sustainable solution

- Saves up to 90% Energy

Highlights

Learn about light



Colour temperature: light can have different colour temperatures, indicated in units called Kelvin (K). Lamps with a low Kelvin value produce a warm, more tranquil light, while those with a higher Kelvin value produce a cool, more energising light. CRI: the colour rendering index (CRI) is used to describe the effect of a light source on

colour appearance. Natural sunlight has a CRI of 100. The CRI of Philips LED lamps is always higher than 80, which ensures that colours are shown as true and natural.

Replaces standard incandescents



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, energy-saving standard LED bulb. The perfect sustainable replacement for traditional standard incandescent bulbs.

Saves up to 90% Energy



Enjoy the energy saving of LEDs without sacrificing light quality. Instantly save over 90% in energy by replacing your existing incandescent or halogen lamps

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional bulb
- Socket: B22
- Dimmable: No

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 806 lm
- Warm-up time to 60% light: 0.5
- Colour Code: 827 | CCT of 2700K
- Luminous efficacy (rated) (nom.): 100 lm/W

Packaging information

- EAN: 8718699775469
- EOC: 871869977546900
- Product title: LED 60W A60 B22 WW FR ND 3PF/6 DISC

Power consumption

- Power factor: 0.55
- Voltage: 220-240 V
- Wattage equivalent: 60 W
- Energy efficiency label (EEL): F
- Power: 8 W
- Energy consumption kWh/1,000 hours: 8

Product dimensions and weight

- Overall height: 105 mm
- Overall length: 105 mm
- Overall width: 60 mm

Technical specifications

- Frequency: 50-60
- EPREL Registration Number: 397617

Packaging dimensions and weight

- EAN/UPC - product: 8718699775469
- Net weight: 0.17 kg
- Gross weight: 0.2 kg
- Height: 14.5 cm
- Length: 6.1 cm
- Width: 14.9 cm



Issue date: 2025-12-24
Version: 0.170

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com