

PHILIPS

Filament Candle Clear
40W B35 E14 x2

LED

2700K

470 lm

15000 h



8718699777616



Warm white light, no compromise on light quality

Familiar shapes you know and love. They use around 85% less energy than traditional light bulbs thanks to the latest LED energy-saving technology, and last ten times longer.

Choose a simple replacement for your old lamps

- Similar shape and size as standard incandescent bulbs

Create the right light for your home

- Perfect for general room lighting

High-quality LED light that lasts for decades

- Designed for the comfort of your eyes

Highlights

Replaces standard incandescents



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, energy-saving standard LED bulb. The perfect sustainable replacement for traditional standard incandescent bulbs.

Perfect for general lighting



Modern lighting with Philips LED standard bulbs for all-around illumination, perfect for general room lighting.

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional candle
- Socket: E14
- Dimmable: No

Lamp dimensions

- Height: 9.7 cm
- Width: 3.5 cm

Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- LED integrated: Yes

Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 470 lm
- Warm-up time to 60% light: Instant full light
- Colour Code: 827 | CCT of 2700K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Efficacy: 109 lm/W

Packaging information

- EAN: 8718699777616
- EOC: 871869977761601
- Product title: LED classic 40W B35E14WW CL NDRF2SRT6 UK

Power consumption

- Power factor: 0.41
- Voltage: 220-240 V
- Wattage: 4.3 W
- Wattage equivalent: 40 W
- Energy efficiency label (EEL): F
- Energy consumption kWh/1,000 hours: 5

Product dimensions and weight

- Length: 9.7 cm

Technical specifications

- Frequency: 50-60
- Bulb technology: LED
- EPREL Registration Number: 387402

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 8718699777616
- Net weight: 0.03 kg
- Gross weight: 0.07 kg
- Height: 14.6 cm
- Length: 4.6 cm
- Width: 8.5 cm



Issue date: 2026-05-30
Version: 0.275

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com