

PHILIPS

Spot

LED

4.8-3.5-1.5W-50W

GU10

2700-2500-2200



8719514307766



One lamp. Your switch. Three light settings.

Change your room ambience to suit whatever you're doing. With the Philips SceneSwitch LED lamp, you can easily change the setting from bright light, to natural light and to a cosy warm glow. All you need is your existing switch.

High-quality light

- Light all around

Light beyond illumination

- Restore the lamp to the default factory setting
- No dimmer or additional installation needed
- The lamp can memorise your last setting

Highlights

Light all around

Thanks to its innovative, vintage design shape, this LED bulb prevents the shadow that normally appears at the beam spread edge. The result? Natural warm white light all around.

Reset (Sceneswitch)



If multiple lamps are used and they are no longer synchronised, simply toggle the switch (turn it on and off again within 1 second) to restore the lamps to the default factory setting.

Plug and play



Does not require any additional installation or a dimmer switch. This lamp is not suitable for use with dimmers. If used on a dimmer setting, the dimmer is set to 100% brightness.

Auto memory (sceneswitch)



This Scene Switch lamp has a built-in memory chip which will memorise your last light setting if the switch is turned off for longer than 6 seconds. If you don't often switch between activities, the light will be in your favourite mode when you turn it on again.

Specifications

General

- Suitable for accent lighting: Yes

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: GU10
- Dimmable: No

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- LED integrated: Yes

Guarantee

- Warranty period: 2 years

Light characteristics

- Beam angle: 36 degree(s)
- Colour rendering index (CRI): 80
- Colour temperature: 2200-2500-2700 K
- Nominal luminous flux: 355 lm
- Warm-up time to 60% light: 0.5 s
- Colour Code: 827-825-822 | CCT of 2700K/2500K/2200K
- Correlated Colour Temperature (Nom): 2200, 2500, 2700
- Luminous Flux: 355 lm
- Stroboscopic effect: 0.6
- Luminous efficacy (rated) (nom.): 73.00

Miscellaneous

- EyeComfort: Yes

Other characteristics

- EU RoHS compliant: Yes

Packaging information

- EAN: 8719514307766
- EOC: 871951430776600
- Product title: LED SSW 50W GU10 WW 36D ND SRT4

Power

- Power Factor (Fraction): 0.5

Power consumption

- Power factor: 0.5
- Voltage: 220–240 V
- Wattage equivalent: 50
- Energy efficiency label (EEL): F
- Power: 4.8
- Energy consumption kWh/1,000 hours: 5

Product dimensions and weight

- Overall height: 54 mm
- Overall length: 54 mm
- Overall width: 50 mm

Rated values

- Rated lifetime: 15,000
- Rated peak intensity: 600 cd

Technical specifications

- Frequency: 50–60
- Diameter: 50 mm
- Bulb technology: LED
- EPREL Registration Number: 1825223
- Flux measurement reference: Narrow Cone
- Dimmable: No
- Flickering value (PstLM): 1
- Line Frequency: 50 to 60
- Cap base: GU10
- Can it be used in closed luminaires: No

Packaging dimensions and weight

- EAN/UPC - product: 8719514307766
- Net weight: 0.05 kg
- Gross weight: 0.07 kg
- Height: 12.7 cm
- Length: 5.3 cm
- Width: 6.3 cm



Issue date: 2026-03-21
Version: 0.206

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com