

# PHILIPS

Filament Candle  
Clear 40 W B35 B22

LED

2200-2700K


470 lm

15000 h

Dimming



8719514324251



## Experience dimmable, warm white LED light

Philips LED clear candles provide a beautiful, sparkling light effect and an exceptionally long life. Beautiful both switched on and switched off, this light bulb is the perfect match for chandelier fixtures with small (E14) fittings.

### Choose for a sustainable solution

- Better for your wallet and your planet

### Create the right light for your home

- Perfect for decorative fixtures

# Highlights

## **Energy savings of up to 90%**

LED technology provides energy savings of up to 90% compared with your standard bulb. It therefore pays for itself and saves you money year after year. It also helps to protect the environment.

## **Perfect for decorative fixtures**



Modern lighting in Philips LED candles for use in decorative fixtures, such as in chandeliers, ceiling fans, vanity strips and post lights.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional candle
- Socket: B22
- Dimmable: Only with specific dimmers

## Lamp dimensions

- Height: 9.4 cm
- Width: 3.5 cm

## Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000 h

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Light characteristics

- Colour rendering index (CRI): 90
- Colour temperature: 2200-2700 K
- Nominal luminous flux: 470 lm
- Warm-up time to 60% light: Instant full light
- Colour Code: 922-927 | CCT of 2200K-2700K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Efficacy: 138 lm/W

## Packaging information

- EAN: 8719514324251
- EOC: 871951432425100
- Product title: LED classic 40W B35 B22 CL WGD90 SRT4

## Power consumption

- Power factor: 0.6
- Voltage: 220-240 V
- Wattage: 3.4 W
- Wattage equivalent: 40 W
- Energy efficiency label (EEL): D

## Product dimensions and weight

- Length: 9.4 cm

## Technical specifications

- Frequency: 50-60 Hz
- EPREL registration number: 1109141
- Flux measurement reference: Sphere

## Packaging dimensions and weight

- EAN/UPC - product: 8719514324251
- Net weight: 0.01 kg
- Gross weight: 0.03 kg
- Height: 14.6 cm
- Length: 4.6 cm
- Width: 6.3 cm
- Material number (12NC): 929003012401



Issue date: 2024-09-18  
Version: 0.165

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)