

# PHILIPS

Filament Candle  
Frosted 40W P45 E27

LED

3.4W-40W

E27

Warm Glow

Dimming



8719514324497



## Experience dimmable, warm white LED light

Philips LED frosted candles provide a soft, diffuse light effect and an exceptionally long life. With a pure and elegant design, this light bulb is the perfect match for chandelier fixtures with small (E14) fittings.

### Choose for a sustainable solution

- Saves up to 90% Energy

### Create the right light for your home

- Perfect for decorative fixtures

# Highlights

## Saves up to 90% Energy



Enjoy the energy saving of LEDs without sacrificing light quality. Instantly save over 90% in energy by replacing your existing incandescent or halogen lamps

## Perfect for decorative fixtures



Contemporary lighting in Philips LED lustres for use in decorative fixtures such as chandeliers, ceiling fans, vanity strips and post lights.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional lustre
- Socket: E27
- Dimmable: Yes
- Lamp Finish: Frosted
- Bulb material: Glass

## Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Light characteristics

- Colour rendering index (CRI): 90
- Colour temperature: 2200-2700 K
- Nominal luminous flux: 470 lm
- Warm-up time to 60% light: 0.5
- Colour Code: 922-927 | CCT of 2200K-2700K
- Luminous efficacy (rated) (nom.): 138 lm/W

## Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort
- Extra Features: Dimmable, WarmGlow

## Packaging information

- EAN: 8719514324497
- EOC: 871951432449700
- Product title: LED classic 40W P45 E27 WGD90 FR SRT4

## Power consumption

- Power factor: 0.6
- Voltage: 220-240 V
- Wattage equivalent: 40 W
- Energy efficiency label (EEL): D
- Power Consumption: 3.4 W
- Energy consumption kWh/1,000 hours: 4

## Product dimensions and weight

- Overall height: 78 mm
- Overall length: 78 mm
- Overall width: 45 mm

## Technical specifications

- Frequency: 50-60
- EPREL Registration Number: 1109146

**Packaging dimensions and weight**

- EAN/UPC – product: 8719514324497
- Net weight: 0.02 kg
- Gross weight: 0.04 kg
- Height: 12.7 cm
- Length: 5.3 cm
- Width: 6.3 cm



Issue date: 2025-11-12  
Version: 0.421

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)