

PHILIPS

June Wall Light 12W
E27 P45 No-bulb

myGarden

No bulb

Antracite

Sensor; Water Resistant



8719514385306



Always light when you come home

Add contemporary style to your garden. This anthracite Philips myGarden wall light with motion sensor catches the eye with its sleek form. It casts warm white energy-saving light and it gives you a warm welcome every time you come home.

Feel welcomed home with light

- Welcoming and reassuring light
- Easy-to-set-up sensor

Design your garden with light

- Decorative outdoor lighting
- Choose contemporary style
- Choose outdoor wall lights
- High-quality aluminium and superior synthetics

Light up your garden with high-quality light

- Energy saving
- Philips bulb always included
- Powerful light

Experience outdoor lighting easily

- Weather-proof

Highlights

Welcoming and reassuring light

The motion sensor switches on automatically when you come home and informs you when someone arrives.

Easy-to-set-up sensor



A simple set-up procedure makes it easy to select when and for how long the automatic sensor switches on the lamp(s).

Decorative outdoor lighting

Outdoor lighting can improve the look of your garden or outside space, illuminating eye-catching features, lighting pathways with style or creating the perfect ambience for those memorable evenings with friends and family. That's why Philips has created myGarden, a range of beautiful decorative outdoor lighting with the flair and functionality to help you make the most of your outdoor space in your own style.

Choose contemporary style

Designed in Europe, this lamp has a unique design signature to help you create a contemporary outdoor look.

Choose outdoor wall lights

Make the most of your outdoor space with this wall light, perfect for mounting close to your front door or on your terrace walls.

High quality material

This Philips lamp is made specifically for outdoor spaces. It's hard-wearing and built to last, so it will light up your garden night after night. It's constructed from high-quality die-cast aluminium and superior synthetics.

Energy saving



This Philips light conserves energy compared to traditional light sources, helping you to save money on your electricity bills and do your bit for the environment.

Philips bulb always included



High-quality Philips EcoLamp energy-efficient light lamps are included in the box for achieving the best light effect.

Powerful light

This outdoor lamp provides powerful warm white light. A bright pool of light to light up your garden or patio.

Weather-proof



This Philips outdoor lamp is specially designed for humid outdoor environments and has undergone rigorous tests to ensure its water resistance. The IP level is described by two figures: the first one refers to the protection level against dust, the second against water. This lamp is designed with IP44: it is protected against splashing water. This product is most common and ideal for general outdoor use.

Specifications

Design and finishing

- Colour: Anthracite
- Material: Metal

Durability

- Nominal lifetime: 10,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with the Hue app and switches: No
- Fully weatherproof: Yes
- LED integrated: No
- Motion sensor: Yes

Garden area

- Garden area: Garden and Patio

Miscellaneous

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: No
- Extra Features: Sensor, Water Resistant

Product dimensions and weight

- Net weight: 0.558 kg
- Overall height: 195 mm
- Overall length: 195 mm
- Overall width: 135 mm

Service

- Warranty: 2 year(s)

Technical specifications

- Mains power: 50–60 Hz
- Energy class included light source: bulb not included
- Fitting/cap: E27
- IP code: IP44 | Wire-protected and splash-proof
- Class of protection: Class II – Double Insulated
- Light source replaceable: Yes
- Number of light sources: 1

Packaging dimensions and weight

- EAN/UPC - product: 8719514385306
- Net weight: 0.56 kg
- Gross weight: 0.88 kg
- Height: 16.3 cm
- Length: 21 cm
- Width: 21 cm



Issue date: 2026-01-31
Version: 0.238

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com