

PHILIPS

Fragrance Wall Light
24W E27 No-bulb

myGarden

Fragrance
anthracite



8719514385405



Saving in style

Go for outdoor lighting that adds a warm light glow to long summer evenings. This Philips anthracite wall light casts warm white energy-saving light. Meanwhile, it creates beautiful bi-directional light effects on your wall.

Sustainable light solutions

- Ultra-long lamp life
- Energy saving

Bring design into your garden

- Choose contemporary style
- Choose outdoor wall lights

Combine ambience and convenience

- Welcoming warm white light glow

Special characteristics

- Bi-directional light effect
- Weather-proof

Highlights

Ultra-long lamp life



Philips lamp included with an ultra-long lamp life, up to 20,000 hours.

Energy saving



This Philips light conserves energy compared to traditional light sources, helping you to save money on your electricity bills and do your bit for the environment.


Choose contemporary style

Designed in Europe, this lamp has a unique design signature to help you create a contemporary outdoor look.

Choose outdoor wall lights

Make the most of your outdoor space with this wall light, perfect for mounting close to your front door or on your terrace walls.

Welcoming warm white light



Philips outdoor is a range of outdoor lamps that creates a beautifully warm welcoming light. The light colour temperature is 2,700 Kelvin. It also provides plenty of light for clear visibility so that you can use your outside space however you like after hours, and relax knowing that it'll be safe and secure throughout the night.

Bi-directional light effect

Bi-directional light effect for general garden illumination.

Weather-proof



This Philips outdoor lamp is specially designed for humid outdoor environments and has undergone rigorous tests to ensure its water resistance. The IP level is described by two figures: the first one refers to the protection level against dust, the second against water. This lamp is designed with IP44: it is protected against splashing water. This product is most common and ideal for general outdoor use.

Specifications

Design and finishing

- Colour: Anthracite
- Material: Metal

Durability

- Nominal lifetime: 10,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Fully weatherproof: Yes
- LED integrated: No

Garden area

- Garden area: Garden and Patio

Miscellaneous

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: No
- Extra Features: Water Resistant

Product dimensions and weight

- Net weight: 1.000 kg
- Overall height: 113 mm
- Overall length: 290 mm
- Overall width: 124 mm

Service

- Warranty: 2 year(s)

Technical specifications

- Mains power: 50-60 Hz
- Energy class included light source: bulb not included
- Fitting/cap: E27
- Wattage bulb included: -
- IP code: IP44 | Wire-protected and splash-proof
- Class of protection: Class I – Earthed
- Number of light sources: 1

Packaging dimensions and weight

- EAN/UPC – product: 8719514385405
- Net weight: 1.1 kg
- Gross weight: 1.3 kg
- Height: 30.5 cm
- Length: 12.3 cm
- Width: 13.1 cm



Issue date: 2025-11-12
Version: 0.285

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com