

# PHILIPS

Bridge Wall Light  
15W E27 No-bulb

Ecomoods

No bulb

Antracite

Water Resistant



8719514385801



## Saving in style

Enjoy lazy evenings in the garden with this elegant antracite outdoor wall light. It welcomes you with warm white light, ideal for general lighting in the garden. Create a stunning atmosphere while making an architectural statement.

### Sustainable light solutions

- Up to 80% energy saving
- Ultra-long lamp life
- Made with robust and reliable high quality material

### Bring design into your garden

- Stylish contemporary designs for your garden
- Eye for detail, made with premium and elegant materials
- A full range of available applications

### Combine ambience and convenience

- Welcoming warm white light glow

### Special characteristics

- IP 44, designed for outdoor use

# Highlights

## Energy efficient



Philips outdoor is a range of affordable outdoor lighting products for the garden that combines contemporary designs with the latest energy-efficient technology. It saves up to 80% energy compared to traditional light sources. The result is as good for the planet as it keeps the money in your pocket where it belongs, year after year.

## Ultra-long lamp life



Philips lamp included with an ultra-long lamp life, up to 20,000 hours.

## High quality material



Built to last. Every piece in the Philips outdoor lighting collection uses high-quality materials and components to resist to outdoor conditions.

## Stylish contemporary designs

The contemporary designs by Philips are stylish but understated, beautiful by day or night without overwhelming your garden or terrace. There's a full range of lights to choose from, so there's bound to be one to match your outside space and taste.

## Eye for detail




Each piece is constructed from high quality components and hard wearing materials like die-cast aluminium and stainless steel.

## Many applications

Ideal outdoor lighting for a garden, terrace, pathway or balcony, Philips outdoor's wall, post, pedestal and ceiling lights create a cosy, relaxing atmosphere when the sun goes down, as well as providing the reassurance of being able to see safely after dark.

## Welcoming warm white light



Philips outdoor is a range of outdoor lamps that creates a beautifully warm welcoming light. The light colour temperature is 2,700 Kelvin. It also provides plenty of light for clear visibility so that you can use your outside space however you like after hours, and relax knowing that it'll be safe and secure throughout the night.

## Designed for outdoor use



IP44 protection means that it's designed for outdoor use, so you can be sure your outdoor lights will brighten up your garden come rain, shine or snow.

# Specifications

## Design and finishing

- Colour: Anthracite
- Material: Metal

## Durability

- Nominal lifetime: 10,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Fully weatherproof: Yes
- LED integrated: No

## Garden area

- Garden area: Garden and Patio

## Miscellaneous

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: No
- Extra Features: Water Resistant

## Product dimensions and weight

- Net weight: 0.889 kg
- Overall height: 212 mm
- Overall length: 118 mm
- Overall width: 101 mm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Bulb technology: LED
- Mains power: 50-60 Hz
- Energy class included light source: bulb not included
- Fitting/cap: E27
- Wattage bulb included: -
- IP code: IP44 | Wire-protected and splash-proof
- Class of protection: Class II – Double Insulated
- Number of light sources: 1

## The bulb

- Software upgradable: No

## What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

## Packaging dimensions and weight

- EAN/UPC - product: 8719514385801
- Net weight: 0.89 kg
- Gross weight: 1.23 kg
- Height: 25.6 cm
- Length: 11.8 cm
- Width: 13.2 cm



Issue date: 2026-04-15  
Version: 0.334

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)