

# PHILIPS

Spot 50W PAR16  
GU10 x3

LED

2700K

380 lm

15000 h



8719514393998



## Bright LED lighting

Philips LED light bulbs provide high-quality light, an exceptionally long life and immediate, significant energy savings.

### High-quality light

- Learn about light

### Choose a simple replacement for your old lamps

- Similar shape and size as standard incandescent bulbs

### Choose for a sustainable solution

- Saves up to 90% Energy

# Highlights

## Learn about light



Colour temperature: light can have different colour temperatures, indicated in units called Kelvin (K). Lamps with a low Kelvin value produce a warm, more tranquil light, while those with a higher Kelvin value produce a cool, more energising light. CRI: the colour rendering index (CRI) is used to describe the effect of a light source on

colour appearance. Natural sunlight has a CRI of 100. The CRI of Philips LED lamps is always higher than 80, which ensures that colours are shown as true and natural.

## Replaces standard incandescents



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, energy-saving standard LED bulb. The perfect sustainable replacement for traditional standard incandescent bulbs.

## Saves up to 90% Energy



Enjoy the energy saving of LEDs without sacrificing light quality. Instantly save over 90% in energy by replacing your existing incandescent or halogen lamps

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: GU10
- Lamp Finish: Clear
- Dimmable: No
- Bulb material: Plastic

## Durability

- Number of switch cycles: 30,000
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- LED integrated: Yes

## Light characteristics

- Beam angle: 36
- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 380 lm
- Warm-up time to 60% light: 0.5
- Colour Code: 827 | CCT of 2700K
- Luminous efficacy (rated) (nom.): 80

## Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort

## Packaging information

- EAN: 8719514393998
- EOC: 871951439399800
- Product title: LED 50W GU10 WW 36D 3PF/8 DISC

**Power consumption**

- Power factor: 0.53
- Voltage: 220–240 V
- Wattage equivalent: 50
- Energy efficiency label (EEL): F
- Power: 4.7
- Energy consumption kWh/1,000 hours: 5

**Product dimensions and weight**

- Overall height: 56 mm
- Overall length: 56 mm
- Overall width: 50 mm

**Rated values**

- Rated peak intensity: 700 cd

**Technical specifications**

- Frequency: 50–60
- Bulb technology: LED
- EPREL Registration Number: 1825208

**The bulb**

- Software upgradable: No

**What's supported**

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

**Packaging dimensions and weight**

- EAN/UPC - product: 8719514393998
- Net weight: 0.09 kg
- Gross weight: 0.13 kg
- Height: 14.4 cm
- Length: 5.1 cm
- Width: 10.5 cm



Issue date: 2026-05-30  
Version: 0.355

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)