

# PHILIPS

Reflector 75W  
PAR30S E27

LED

9.5 W-75 WW

E27

Warm White

Dimming



8719514443266



## Durable LED accent lighting with a focused beam

This directional LED lamp provides a focused beam of dimmable warm white light and is an excellent dimmable replacement for traditional reflector lamps

### High-quality light

- Learn about light

### Choose a simple replacement for your old lamps

- Similar shape and size as halogen reflectors

### Create the right light for your home

- Perfect for accent lighting

# Highlights

## Learn about light



Colour temperature: light can have different colour temperatures, indicated in units called Kelvin (K). Lamps with a low Kelvin value produce a warm, more tranquil light, while those with a higher Kelvin value produce a cool, more energising light. CRI: the colour rendering index (CRI) is used to describe the effect of a light source on colour appearance. Natural sunlight

has a CRI of 100. The CRI of Philips LED lamps is always higher than 80, which ensures that colours are shown as true and natural.

## Replaces halogen spots



With its beautifully shaped design and familiar dimensions, this is a modern lighting, LED reflector. The perfect sustainable replacement for traditional halogen reflectors.

## Perfect for accent lighting



Contemporary lighting with a familiar narrow-angle light output (25 degrees), this LED reflector is suitable for both accent lighting and general purpose lighting. It can be used in recessed cans and track light fixtures, and is ideal for use in kitchens, kitchen island lighting living rooms and dining rooms.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: E27
- Lamp Finish: Clear
- Dimmable: Yes
- Bulb material: Glass

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 25,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Light characteristics

- Beam angle: 25 degree(s)
- Colour rendering index (CRI): 90
- Colour temperature: 2700 K
- Nominal luminous flux: 740 lm
- Warm-up time to 60% light: 0.5
- Colour Code: 927 | CCT of 2700K
- Luminous efficacy (rated) (nom.): 77 lm/W

## Miscellaneous

- Extra Features: Dimmable

## Packaging information

- EAN: 8719514443266
- EOC: 871951444326600
- Product title: LED Classic 75W PAR30S WW 25D D 1PF/4

#### Power consumption

- Power factor: 0.7
- Voltage: 220–240 V
- Wattage equivalent: 75 W
- Energy efficiency label (EEL): F
- Power Consumption: 9.5 W
- Energy consumption kWh/1,000 hours: 10

#### Product dimensions and weight

- Overall height: 86 mm
- Overall length: 86 mm
- Overall width: 95 mm

#### Rated values

- Rated peak intensity: 3000 cd

#### Technical specifications

- Frequency: 50–60
- EPREL Registration Number: 1121746

#### Packaging dimensions and weight

- EAN/UPC – product: 8719514443266
- Net weight: 0.16 kg
- Gross weight: 0.3 kg
- Height: 18.2 cm
- Length: 10.2 cm
- Width: 13 cm



Issue date: 2025-11-29  
Version: 0.316

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)