

PHILIPS

Arbour Post Light
3.8W

Outdoor luminaires

3000K

Anthracite

Water Resistant



8719514490260



Our most energy-efficient LED lights yet

Philips has developed an Ultra Efficient outdoor light that uses new technology to cut carbon emissions, reduce material waste and lower energy usage. With an amazing 50,000 hour lifetime it lasts more than 3 times longer than the Philips LED outdoor light equivalents – and uses a miniscule 50% of the energy. Just what is needed for a more sustainable planet.

Sustainable light solutions

- Ultra Efficient

Advanced LED light

- 5-year warranty on LED system

Premium quality

- High-quality aluminium and superior synthetics

Designed for outdoors


- IP44 – weatherproof

High-quality light

- Bright white light 3,000 K

Highlights

Ultra Efficient



Consumes at least 50% less energy compared to equivalent standard LED lights from Philips.

5-year warranty on LED system



In addition to the standard 2-year warranty offered for this luminaire, Philips also offers a 5-year warranty on the LED system (the LED module and driver).

High-quality aluminium and superior synthetics




This Philips light is made specifically for outdoor spaces. It's hard-wearing and built to last, so it will light up your garden night after night. It's constructed from high quality die-cast aluminium and superior synthetics.

IP44 – weatherproof



This Philips outdoor light is especially designed for humid outdoor environments and has been tested rigorously to ensure water resistance. Its IP44 rating means that it has been certified to offer ingress protection against dust and splashing water – perfect for general outdoor use.

Bright white light 3,000 K



Did you know that different shades of white light are identified by different colour temperatures, measured in Kelvin (K)? Lower colour temperatures produce a warm, cosy white light, while higher colour temperatures produce a cool, more energising white light. This luminaire produces bright white light at 3,000 K.

Specifications

Design and finishing

- Colour: Anthracite
- Material: Metal

Durability

- Nominal lifetime: 50,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Anti-rust anti-dust: Yes
- Bi-directional light beams: No
- Day-and-night sensor: No
- Fully weatherproof: Yes
- LED integrated: Yes
- Motion sensor: No
- Solar Energy: No
- Warm White Light: No
- Centrepiece: No

Garden area

- Garden area: Garden and Patio

Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 3000 K

Miscellaneous

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Post Lights
- EyeComfort: No
- LED innovations: UltraEfficient
- Extra Features: Water Resistant

Product dimensions and weight

- Net weight: 2 kg
- Overall height: 770 mm
- Overall length: 100 mm
- Overall width: 100 mm

Service

- Warranty: 2 year(s)

Technical specifications

- Total lumen output fixture: 800
- Light colour: 3000K
- Mains power: 220–240
- Energy class included light source: A
- IP code: IP44 | Wire-protected and splash-proof
- Class of protection: Class II – Double Insulated
- Light source replaceable: Yes

Packaging dimensions and weight

- EAN/UPC – product: 8719514490260
- Net weight: 2 kg
- Gross weight: 2.19 kg
- Height: 78.5 cm
- Length: 11 cm
- Width: 11 cm



Issue date: 2025-08-30
Version: 0.210

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com