

PHILIPS

Wall mount

ProjectLine

Round shape

4000K natural white light

1400 lm

PHILIPS

ProjectLine

LED wall mount

1400
lm

15W

4000K

LED

35,000h
IP65

REAL
PROs

REAL
QUALITY



Professional quality for your project

8719514954311



Professional quality for your project

Energy efficient and professional quality LED (indoor) wall light. ProjectLine wall-mount supports energy saving and can be mounted on the wall and ceiling. Ideal for corridors, (public) entrance areas, porch lighting, security lighting and staircase lighting with its natural white light.

Sustainable choice

- Save energy from the moment you flick the switch

Choose for the high-quality light

- You can trust what the Philips packaging is saying

Durability

- Long life span up to 35,000 hours

Highlights

Energy efficient

All Philips energy savers save energy from the moment you flick the switch. During their lifetime they use fewer kW and thus also result in a lower energy bill. The level of energy saving differs per lamp type and technology.

Reliable quality

Philips keeps its promises about lamp performance. You can trust what the Philips packaging is saying about light output, lifetime and wattage equivalence to incandescent lamps.

Long life span up to 35,000 hours

Philips LED technology extends your product's lifetime up to 35,000 hours.

Specifications

Design and finishing

- Colour: White
- Material: PVC
- Optical cover/lens finish: Opal
- Optical cover/lens material: Polycarbonate

Durability

- Ambient temperature range: -20 to +40 °C

Extra feature/accessory incl.

- LED integrated: Yes

Light characteristics

- Beam angle: 110
- Colour rendering index (CRI): 80
- Luminous flux tolerance: +/-10%
- Color Code: 840 neutral white
- Constant light output: No
- Correlated Colour Temperature (Nom): 4000
- Initial chromaticity: (0.38,0.38) SDCM <6
- Light source replaceable: No
- Luminaire light beam spread: 110°
- Luminous Flux: 1,400
- Maximum dim level: Not applicable
- Optic material: Polycarbonate
- Optic type: Wide beam
- Performance ambient temperature Tq: 25 °C
- Saturated Red (R9): <50
- Stroboscopic effect: 1.6
- Luminous efficacy (rated) (nom.): 90
- Unified Glare Rating (CEN): Not applicable

Miscellaneous

- Especially designed for: Garden, Patio, Hotel, Restaurant
- Extra Features: ProjectLine, Water Resistant

Other characteristics

- CE mark: Yes
- EU RoHS compliant: Yes
- Photobiological risk: Photobiological risk group 0 @200mm to EN62778
- Photobiological risk specification: 0.2 m

Power

- Input Voltage: 220 to 240
- Inrush current: 8
- Inrush time: 1.2
- Power Factor (Fraction): 0.7

Power consumption

- Power: 15
- Power consumption tolerance: +/-10%

Product dimensions and weight

- Overall height: 66

Service

- Warranty: 3 year(s)

Technical specifications

- Diameter: 182 mm
- Bulb technology: LED
- IP code: IP65
- Class of protection: Class II – Double Insulated
- Connection: Screw connection block 2-pole
- Control gear failure rate at median useful life 35,000 h: 5
- Dimmable: No
- Driver/power unit/transformer: -
- Driver included: Yes
- Flammability mark: For mounting on normally flammable surfaces
- Flickering value (PstLM): 1
- Glow-wire test: Temperature 650 °C, duration 30 s
- Line Frequency: 50 or 60
- Mech. impact protection code: IK06 | 1 J
- Number of gear units: Unit
- Number of products on MCB (16 A type B): 10

- Suitable for random switching: Yes

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 8719514954311
- Net weight: 0.39 kg
- Gross weight: 0.46 kg
- Height: 7.2 cm
- Length: 18.4 cm
- Width: 18.4 cm



Issue date: 2026-05-13
Version: 0.272

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com