

# PHILIPS

## Batten

### ProjectLine

120 cm

3000K warm white light

2,700 lm

8719514954366



## Professional quality for your project

Energy efficient LED lighting battens, professional LEDs for varied applications. ProjectLine batten light supports energy saving and is applicable for a wide range of applications. The lighting batten is suitable for wall (horizontal) and ceiling mounted with warm white light.

### Sustainable choice

- Save energy from the moment you flick the switch

### Choose for the high-quality light

- You can trust what the Philips packaging is saying

### Durability

- Long life span up to 35,000 hours

# Highlights

## Energy efficient

All Philips energy savers save energy from the moment you flick the switch. During their lifetime they use fewer kW and thus also result in a lower energy bill. The level of energy saving differs per lamp type and technology.

## Reliable quality

Philips keeps its promises about lamp performance. You can trust what the Philips packaging is saying about light output, lifetime and wattage equivalence to incandescent lamps.

## Long life span up to 35,000 hours

Philips LED technology extends your product's lifetime up to 35,000 hours.

# Specifications

## Design and finishing

- Colour: White
- Material: PVC
- Optical cover/lens finish: Opal
- Optical cover/lens material: Polycarbonate

## Durability

- Ambient temperature range: -20 to +40 °C

## Light characteristics

- Beam angle: 120 degree(s)
- Colour rendering index (CRI): 80
- Luminous flux tolerance: +/-10%
- Color Code: 830 warm white
- Constant light output: No
- Correlated Colour Temperature (Nom): 3000
- Initial chromaticity: (0.43,0.40) SDCM <6
- Light source replaceable: No
- Luminaire light beam spread: 120°
- Luminous Flux: 2,700 lm
- Maximum dim level: Not applicable
- Optic material: Polycarbonate
- Optic type: Symmetrical
- Saturated Red (R9): <50
- Performance ambient temperature Tq: 25 °C
- Stroboscopic effect: 1.6
- Unified Glare Rating (CEN): Not applicable
- Luminous efficacy (rated) (nom.): 92 lm/W

## Miscellaneous

- Especially designed for: Hotel, Restaurant, Garden, Patio
- Extra Features: ProjectLine, Water Resistant

## Other characteristics

- CE mark: Yes
- EU RoHS compliant: Yes
- Photobiological risk: Photobiological risk group 1 @200mm to EN62778
- Photobiological risk specification: 0.2 m

## Power

- Input Voltage: 220-240
- Inrush current: 12.3
- Inrush time: 0.197
- Power Factor (Fraction): 0.9

## Power consumption

- Power Consumption: 30
- Power consumption tolerance: +/-10%

## Product dimensions and weight

- Overall height: 27
- Overall length: 1,200
- Overall width: 70

## Service

- Warranty: 2 year(s)

**Technical specifications**

- IP code: IP20 | Finger-protected
- Class of protection: Class II – Double Insulated
- Cable: Cable 0.2 m without plug
- Connection: Flying leads/cables
- Control gear failure rate at median useful life 35,000 h: 5
- Dimmable: No
- Driver included: Yes
- Fixation material: Stainless steel
- Flammability mark: For mounting on normally flammable surfaces
- Flickering value (PstLM): 1
- Glow-wire test: Temperature 650 °C, duration 30 s

- Line Frequency: 50 or 60
- Mech. impact protection code: IK03 | 0.3 J
- Number of gear units: Unit
- Number of products on MCB (16 A type B): 75
- Suitable for random switching: Yes

**Packaging dimensions and weight**

- EAN/UPC – product: 8719514954366
- Net weight: 0.28 kg
- Gross weight: 0.36 kg
- Height: 3 cm
- Length: 121.8 cm
- Width: 7.3 cm



Issue date: 2025-11-01  
Version: 0.323

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)