

# PHILIPS

## Floodlight

ProjectLine

10 W

3000K warm white light



Professional quality for your project

8719514954397



## Professional quality for your project

Water tight, robust LEDs for outdoor use. ProjectLine floodlight supports energy saving, and is robust with its metal material and weather protection. Ideal to light up areas in front/back of (public) buildings, such as car parks, driveways, gardens or working locations.

### Sustainable choice

- Save energy from the moment you flick the switch

### Choose for the high-quality light

- You can trust what the Philips packaging is saying

### Durability

- Long life span up to 35,000 hours

# Highlights

## Energy efficient

All Philips energy savers save energy from the moment you flick the switch. During their lifetime they use fewer kW and thus also result in a lower energy bill. The level of energy saving differs per lamp type and technology.

## Reliable quality

Philips keeps its promises about lamp performance. You can trust what the Philips packaging is saying about light output, lifetime and wattage equivalence to incandescent lamps.

## Long life span up to 35,000 hours

Philips LED technology extends your product's lifetime up to 35,000 hours.

# Specifications

## Design and finishing

- Colour: Black
- Material: Metal
- Optical cover/lens finish: Clear
- Optical cover/lens material: Tempered glass
- Optical cover/lens shape: Flat
- Optical cover type: Glass

## Durability

- Ambient temperature range: -40 to +50 °C

## Environmental

- Sustainability rating: Unclassified

## Extra feature/accessory incl.

- LED integrated: Yes

## Light characteristics

- Colour rendering index (CRI): 80
- Luminous flux tolerance: +/-10%
- Color Code: 830 warm white
- Correlated Colour Temperature (Nom): 3000
- Init. Colour Rendering Index Tolerance: 0
- Initial chromaticity: (0.440, 0.403)
- SDCM <6
- Lamp family code: LED
- Light source engine type: LED
- Light source replaceable: No
- Luminaire light beam spread: 110°
- Luminous Flux: 900
- Optic material: Glass
- Optic type outdoor: Symmetrical
- Reflector material: Polycarbonate
- Performance ambient temperature Tq: 25 °C
- Luminous efficacy (rated) (nom.): 90
- Upwards light output ratio: 0

## Miscellaneous

- Especially designed for: Garden, Patio, Hotel, Restaurant
- Extra Features: ProjectLine, Water Resistant

## Other characteristics

- CE mark: Yes
- ENEC mark: -
- EU RoHS compliant: Yes
- Photobiological risk: Photobiological risk group 1 @200mm to EN62778
- Photobiological risk specification: 0.2 m

**Power**

- Input Voltage: 220 to 240
- Inrush current: 0.31
- Inrush time: 0.056
- Power Factor (Fraction): 0.9

**Power consumption**

- Power: 10
- Power consumption tolerance: +/-10%

**Product dimensions and weight**

- Overall height: 28
- Overall length: 107
- Overall width: 102

**Service**

- Warranty: 2 year(s)

**Technical specifications**

- Bulb technology: LED
- IP code: IP65 | Dust-tight and jet-proof
- Class of protection: Class I – Earthed
- Cable: Cable 0.3 m without plug
- Connection: Flying leads/cables
- Control gear failure rate at median useful life 35,000 h: 5
- Dimmable: No
- Driver/power unit/transformer: -
- Driver included: Yes
- Effective projected area: 0.003
- Fixation material: Steel
- Flammability mark: For mounting on normally flammable surfaces
- Line Frequency: 50 or 60
- Mech. impact protection code: IK06 | 1 J
- Mounting device: Mounting bracket adjustable
- Number of gear units: Unit
- Number of products on MCB (16 A type B): 211
- Surge Protection (Common/Differential): EN61547 (L-L 1 kV, L-G 2 kV)

**Packaging dimensions and weight**

- EAN/UPC - product: 8719514954397
- Net weight: 0.19 kg
- Gross weight: 0.21 kg
- Height: 4 cm
- Length: 11.5 cm
- Width: 11.5 cm



Issue date: 2026-03-21  
Version: 0.243

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.