



Filament clear 60 W A60 B22



The WiZ A60 filament ultra efficient smart bulb is the most energy-efficient smart bulb in the WiZ ecosystem. This A-class rated smart light bulb that consumes 40% less energy than standard LED and connected LED light bulbs. With SpaceSense, two or more bulbs can act as motion sensors, automatically turning on when you're present in a room and off when you're not. You can support your daily and weekly routines by scheduling WiZ lights to activate only when and how you need them, anticipating your needs and saving you energy. Visualise and track energy use with the WiZ app, giving you unprecedented insight into and control over your lighting's energy consumption.

PRODUCT HIGHLIGHTS

- Tunable white smart bulb
- Up to 903 lumens
- Easy plug and play
- Control with app or voice



Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



Matter Certified

This product is Matter certified. You can set it up and control it with your preferred smart home platform and make it work seamlessly with other Matter Certified devices.



Exclusive SpaceSense™ light that turns on with movement

WiZ's SpaceSense technology turns your lights into motion sensors. With a minimum of two WiZ lights in a room, you can activate the SpaceSense feature in the WiZ app and get the lights to turn on and off automatically with motion detection. It's simple. It's SpaceSense. It's WiZ.



Monitor your energy consumption

Get an overview of the energy consumption of your lights with the WiZ app. Easily access a weekly or daily report to help you stay on top of your energy consumption at home.



Set up lights to follow your own schedule

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.



Set the right ambience with tunable warm to cool white light

Choose from a wide range of energising cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor
Lamp shape: A60
Socket: B22
Technology: Smart Wi-Fi
Type of glass: Clear
Dimmable: Wireless Dim

LAMP DIMENSIONS

Height: 12.6 cm
Weight: 0.055 kg
Width: 6 cm

DURABILITY

Average life (at 2.7 hrs/day): 51 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 50,000
Nominal lifetime: 50,000 h

LIGHT CHARACTERISTICS

Beam angle: 300 degree(s)
Colour consistency: 6 SDCM
Colour rendering index (CRI): 80
Colour temperature: 2700-4000 K
Light Colour Category: Tunable white
Nominal luminous flux: 903 lm
Starting time: <0.5 s
Warm-up time to 60% light: Instant full light

OTHER CHARACTERISTICS

Lamp current: 42 mA
Efficacy: 210 lm/W

PACKAGING INFORMATION

EAN: 8720169078208
EOC: 872016907820800
Product title: Wi-Fi BLE 60W A60 B22
827-40 TW EELA 1PF

POWER CONSUMPTION

Power factor: 0.48
Voltage: AC 220-240 V
Wattage: 4.3 W
Energy efficiency label (EEL): A

PRODUCT DIMENSIONS AND WEIGHT

Length: 12.6 cm

RATED VALUES

Rated beam angle: 300 degree(s)
Rated lifetime: 50,000 h
Rated luminous flux: 903 lm
Rated power: 4.3 W

TECHNICAL SPECIFICATIONS

Frequency: 50-60 Hz
EPREL Registration Number: 2004762
Flux measurement reference: Sphere



© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.