

PHILIPS

UltraEfficient Recessed
Light 145mm Square 4.8W

Ultra Efficient

4000K

White

8720169212800



UltraEfficient Downlight, provide most energy saving solution for you

Philips has developed an Ultra Efficient Downlight that uses new technology to cut carbon emissions, reduce material waste and lower energy usage. With an amazing 50,000-hour lifetime, it lasts more than three times longer than the Philips LED Downlight equivalents – and uses a miniscule 50% of the energy. Just what is needed for a more sustainable planet.

Sustainable light solutions

- Philips offers a 5-year warranty on the LED module and driver

Light effect

- High-quality diffuser Soft light with uniform distribution

Material and finishing

- High-quality metal material


Highlights

5-year warranty on LED system




On top of the standard 2-year warranty for this lamp, Philips offers a 5-year warranty on the LED system, meaning the LED module and the driver in this lamp.

High-quality diffuser Soft light with uniform distribution



This high-quality diffuser distributes soft light evenly around your rooms.

High-quality metal material



Durable and attractive metal material for a strong finish.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: RoundRectangle

Design and finishing

- Colour: White
- Material: Metal, Plastic

Durability

- Average life (at 2.7 hrs/day): 51 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 25,000
- Nominal lifetime: 50,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 110 degree(s)
- Colour consistency: 5 SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 4000 K
- Warm-up time to 60% light: 2
- Luminous efficacy (rated) (nom.): 161 lm/W

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Office
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: Yes
- LED innovations: UltraEfficient

Other characteristics

- Lamp current: 50.5 mA

Power consumption

- Power factor: 0.4

Product dimensions and weight

- Net weight: 0.165 kg
- Recessed distance: 2 mm
- Overall height: 49.5 mm
- Overall length: 145 mm
- Overall width: 145 mm
- Recessed ceiling cutout: 12.5 cm x 12.5 cm

Packaging dimensions and weight

- EAN/UPC – product: 8720169212800
- Net weight: 0.17 kg
- Gross weight: 0.21 kg
- Height: 14.8 cm
- Length: 5.7 cm
- Width: 14.8 cm

Service

- Warranty: 5 year(s)

Technical specifications

- Diameter: 145 mm
- Total lumen output fixture: 900
- Light colour: 4000
- Mains power: AC 220–240
- Fixture dimmable: No
- Wattage bulb included: 4.8
- IP code: IP20 | Finger-protected
- Class of protection: Class II – Double Insulated



Issue date: 2025-10-11
Version: 0.363

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com