

# PHILIPS

Filament Bulb Frosted  
75W A60 E27 x3

LED

8.5W-75W

E27

Cool White



8720169256873



## Bright LED lighting with excellent light quality

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

### Choose a simple replacement for your old lamps

- Similar shape and size as standard incandescent bulbs

### Choose for a sustainable solution

- You can trust what the Philips packaging is saying.
- Contains no mercury

# Highlights

## Replaces standard incandescents



With its beautifully shaped design and familiar dimensions, this is a

contemporary lighting, energy-saving standard LED bulb. The perfect sustainable replacement for traditional standard incandescent bulbs.

## No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

## Contains no mercury



# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional bulb
- Socket: E27
- Lamp Finish: Frosted
- Dimmable: No
- Bulb material: Glass

## Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- LED integrated: Yes

## Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 4000 K
- Nominal luminous flux: 1055 lm
- Warm-up time to 60% light: Instant full light
- Colour Code: 840 | CCT of 4000K
- Luminous efficacy (rated) (nom.): 124

## Packaging information

- EAN: 8720169256873
- EOC: 872016925687300
- Product title: LED CLA 75W A60 E27 CW FR ND 3PF/6 DISC

## Power consumption

- Power factor: 0.52
- Voltage: AC 220-240 V
- Wattage equivalent: 75
- Power: 8.5
- Energy consumption kWh/1,000 hours: 9

## Product dimensions and weight

- Overall height: 104 mm
- Overall length: 104 mm
- Overall width: 60 mm

## Technical specifications

- Frequency: 50-60
- Bulb technology: LED

## Packaging dimensions and weight

- EAN/UPC - product: 8720169256873
- Net weight: 0.11 kg
- Gross weight: 0.16 kg
- Height: 14.9 cm
- Length: 7.6 cm
- Width: 21.6 cm



Issue date: 2026-03-21  
Version: 0.319

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)