

PHILIPS

Nightingale Wall Light
35W GU10 No-bulb

Outdoor luminaires

No bulb

Black

Water Resistant



8720169266834



Enjoy a beautiful garden with light

This outdoor light is designed around the latest trends and lifestyles to define the ambiance you have always desired.

Ease of use

- No bulb included

Bring design into your garden

- Modern outdoor lighting

Designed for outdoors

- IP44 – weatherproof

Special characteristics

- Bi-directional light effect

Highlights

No bulb included

This luminaire comes without a bulb, which enables you to choose the light output which is best suited to the room and your personal taste. Choosing a Philips LED bulb will ensure a high quality and long-lasting light output.

Modern outdoor lighting

Impressive, bold and minimalist outdoor lighting by Philips. Philips outdoor elegant modern style is the perfect way to grace gardens, pathways and outdoor spaces with light.

IP44 – weatherproof



This Philips outdoor light is especially designed for humid outdoor environments and has been tested rigorously to ensure water resistance. Its IP44 rating means that it has been

certified to offer ingress protection against dust and splashing water – perfect for general outdoor use.

Bi-directional light effect

This Philips outdoor luminaire creates the perfect ambience in your garden or terrace with its bi-directional light effect.

Specifications

Design and finishing

- Colour: Black
- Material: Aluminium

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- 5 year warranty on the LED module: Yes
- Adjustable spot head: No
- Anti-rust anti-dust: Yes
- Bi-directional light beams: No
- Fully weatherproof: Yes
- LED integrated: No
- Motion sensor: No
- Solar Energy: No
- Centrepiece: No

Garden area

- Garden area: Garden and Patio

Miscellaneous

- Especially designed for: Garden and Patio
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: No
- Extra Features: Water Resistant

Product dimensions and weight

- Net weight: 0.6 kg
- Cut out width: 3.5 cm
- Height: 16 cm
- Length: 9.6 cm
- Width: 8 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Mains power: 220–240 V
- Fixture dimmable: No
- Energy class included light source: not applicable
- Fitting/cap: GU10
- Maximum wattage replacement bulb: 35 W
- IP code: IP44
- Class of protection: Class I
- Light source replaceable: Yes
- Number of light sources: 2

Packaging dimensions and weight

- EAN/UPC - product: 8720169266834
- Net weight: 0.6 kg
- Gross weight: 0.64 kg
- Height: 17.8 cm
- Length: 8.5 cm
- Width: 10 cm



Issue date: 2025-04-19
Version: 0.344

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com