

# PHILIPS

Radii Wall Light 1.3W

Outdoor luminaires

3000K

Black

Linkable; Sensor; Solar; Water Resistant



8720169267176



## Our most energy-efficient LED lights yet

Philips has developed an UltraEfficient solar LED outdoor light that uses new technology to cut carbon emissions, reduce material waste and lower energy usage. With an amazing 50,000-hour lifetime, it lasts more than 5 times longer than the Philips LED outdoor light equivalents. Just what is needed for a more sustainable planet.

### Easy installation

- No wiring required

### Sustainable light solutions

- Ultra-efficient solar

### Bring design into your garden

- Choose outdoor wall lights

### Advanced LED light

- 5-year warranty on LED system

### Designed for outdoors

- IP44 – weatherproof

### High-quality light

- Bright white light 3,000 K

# Highlights

## No wiring required



This light is powered entirely by solar energy. No wiring is needed, making these lights easy to position and reposition anywhere in your garden or other outdoor area.

## Ultra-efficient solar



With the Philips Ultra Efficient Solar system, these luminaires provide light for up to 40 hours on a fully-charged battery. Enjoy bright light all night, or even in bad or overcast weather conditions.

## Choose outdoor wall lights

Make the most of your outdoor space with this wall light, perfect for mounting close to your front door or on your terrace walls.

## 5-year warranty on LED system



In addition to the standard 2-year warranty offered for this luminaire, Philips also offers a 5-year warranty on the LED system (the LED module and driver).

## IP44 – weatherproof



This Philips outdoor light is especially designed for humid outdoor environments and has been tested rigorously to ensure water resistance. Its IP44 rating means that it has been certified to offer ingress protection against dust and splashing water – perfect for general outdoor use.

## Bright white light 3,000 K



Did you know that different shades of white light are identified by different colour temperatures, measured in Kelvin (K)? Lower colour temperatures produce a warm, cosy white light, while higher colour temperatures produce a cool, more energising white light. This luminaire produces bright white light at 3,000 K.

# Specifications

## Design and finishing

- Colour: Black
- Material: Plastic

## Durability

- Nominal lifetime: 50,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Adjustable spot head: Not adjustable
- Anti-rust anti-dust: Yes
- Bi-directional light beams: No
- Day-and-night sensor: Yes
- Fully weatherproof: Yes
- LED integrated: Yes
- Motion sensor: Yes
- Solar Energy: Yes
- Warm White Light: No
- Centrepiece: No

## Garden area

- Garden area: Garden and Patio

## Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 3000 K

## Miscellaneous

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: No
- LED innovations: UltraEfficient
- Extra Features: Linkable, Sensor, Solar, Water Resistant

## Power consumption

- Power: 1.3

## Product dimensions and weight

- Net weight: 0.74 kg
- Overall height: 192 mm
- Overall length: 240 mm
- Overall width: 175 mm

## Service

- Warranty: 5 year(s)

## Technical specifications

- Total lumen output fixture: 250
- Bulb technology: LED
- Light colour: 3000K
- Mains power: 4 V
- Fixture dimmable: No
- Energy class included light source: A
- IP code: IP44 | Wire-protected and splash-proof
- Class of protection: Class III – Safe Extra Low Voltage
- Light source replaceable: Yes

## The bulb

- Software upgradable: No

## What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

## Packaging dimensions and weight

- EAN/UPC - product: 8720169267176
- Net weight: 0.74 kg
- Gross weight: 1.13 kg
- Height: 27 cm
- Length: 20 cm
- Width: 20 cm



Issue date: 2026-05-13  
Version: 0.263

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)