

# PHILIPS

Nissa Wall Lights  
1.8 W

Ultra-efficient Solar

3000K

Black

Sensor; Solar; Water Resistant



8720169362086



## Long-lasting solar-powered garden light for all seasons

Philips has developed an Ultra Efficient solar LED outdoor light that uses new technology to cut carbon emissions, reduce material waste and lower energy usage. With an amazing 50,000 hour lifetime it lasts more than 5 times longer than the Philips LED outdoor light equivalents. Just what is needed for a more sustainable planet.

### Easy installation

- No wiring required

### Sustainable light solutions

- Long lifetime up to 50,000 hours

### Premium quality

- High quality material

### Designed for outdoors

- IP44 – weatherproof

### Special characteristics

- Dual-brightness light

8720169362086

**High-quality light**

- Bright white light 3,000 K

# Highlights

## No wiring required



This light is powered entirely by solar energy. No wiring is needed, making these lights easy to position and reposition anywhere in your garden or other outdoor area.

## Long lifetime up to 50,000 hours



Reliable high-quality LED light lasts up to 50,000 hours. You can rest easy knowing that you won't have to worry about maintenance for years, whilst having the perfect light ambience in your home.

## High quality material



This Philips outdoor lamp is made of high-quality materials with superior finishing. This ensures a solid and long-lasting product which is resistant to corrosion and stains in all weather conditions

## IP44 – weatherproof



This Philips outdoor light is especially designed for humid outdoor environments and has been tested rigorously to ensure water resistance. Its IP44 rating means that it has been certified to offer ingress protection against dust and splashing water – perfect for general outdoor use.

## Dual-brightness light

Create a flexible and appealing ambience with the dual-brightness feature. The light dims when idle and automatically brightens when people are present, delivering the right level of light whenever you need it.

## Bright white light 3,000 K



Did you know that different shades of white light are identified by different colour temperatures, measured in Kelvin (K)? Lower colour temperatures produce a warm, cosy white light, while higher colour temperatures produce a cool, more energising white light. This luminaire produces bright white light at 3,000 K.

# Specifications

## Design and finishing

- Colour: Black
- Material: Plastic

## Durability

- Nominal lifetime: 50,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

**Extra feature/accessory incl.**

- Adjustable spot head: Not adjustable
- Anti-rust anti-dust: Yes
- Bi-directional light beams: No
- Day-and-night sensor: Yes
- Fully weatherproof: Yes
- LED integrated: Yes
- Motion sensor: Yes
- Solar Energy: Yes
- Centrepiece: No

**Light characteristics**

- Beam angle: 120
- Colour rendering index (CRI): 80
- Colour temperature: 3000 K

**Miscellaneous**

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: No
- LED innovations: UltraEfficient
- Extra Features: Sensor, Solar, Water Resistant

**Power consumption**

- Power: 1.8

**Product dimensions and weight**

- Net weight: 0.44 kg
- Overall height: 140 mm
- Overall length: 120 mm
- Overall width: 160 mm

**Service**

- Warranty: 5 year(s)

**Technical specifications**

- Total lumen output fixture: 250/25
- Bulb technology: LED
- Light colour: White light
- Mains power: DC 4
- Fixture dimmable: No
- IP code: IP44
- Class of protection: Class III – Safe Extra Low Voltage
- Light source replaceable: No

**The bulb**

- Software upgradable: No

**What's supported**

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

**Packaging dimensions and weight**

- EAN/UPC - product: 8720169362086
- Net weight: 0.44 kg
- Gross weight: 0.59 kg
- Height: 18.8 cm
- Length: 14.5 cm
- Width: 15.5 cm



Issue date: 2026-06-13  
Version: 0.312

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)