

PHILIPS

Calgary Wall Lights
25W E27 No-bulb

Outdoor luminaires

No bulb

Anthracite

Sensor; Water Resistant

8720169391956



Enjoy a beautiful garden

This Philips Calgary outdoor light is designed around the latest trends and lifestyles to define the ambience you have always desired.

Ease of use

- No bulb included

Bring design into your garden

- Stylish contemporary designs for your garden

Premium quality

- High quality material

Designed for outdoors

- IP44 – weatherproof

Special characteristics

- Motion sensor, for convenience and reassurance

Highlights

No bulb included

This luminaire comes without a bulb, which enables you to choose the light output which is best suited to the room and your personal taste. Choosing a Philips LED bulb will ensure a high quality and long-lasting light output.

Stylish contemporary designs for your garden

These contemporary designs by Philips are stylish but understated, beautiful by day or night without overwhelming your garden or terrace. There is a full range of lights to choose from, so there is bound to be one to match your outside space and taste.

High quality material



This Philips outdoor lamp is made of high-quality materials with superior finishing. This ensures a solid and long-lasting product which is resistant to corrosion and stains in all weather conditions.

IP44 – weatherproof



This Philips outdoor light is especially designed for humid outdoor environments and has been tested rigorously to ensure water resistance. Its IP44 rating means that it has been certified to offer ingress protection against dust and splashing water – perfect for general outdoor use.

Motion sensor, for convenience and reassurance



A motion sensor is included to welcome you when you return home or let you know when someone's coming.

Specifications

Design and finishing

- Colour: Anthracite
- Material: Metal

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: Not adjustable
- Anti-rust anti-dust: Yes
- Day-and-night sensor: Yes
- LED integrated: No
- Motion sensor: Yes
- Solar Energy: No
- Centrepiece: No

Miscellaneous

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: No
- Extra Features: Sensor, Water Resistant

Product dimensions and weight

- Net weight: 1.111 kg
- Overall height: 190 mm
- Overall length: 140 mm
- Overall width: 120 mm

Service

- Warranty: 2 year(s)

Technical specifications

- Bulb technology: LED
- Mains power: AC 220-240
- Fixture dimmable: No
- Fitting/cap: E27
- Maximum wattage replacement bulb: 25
- IP code: IP44 | Wire-protected and splash-proof
- Class of protection: Class II – Double Insulated
- Light source replaceable: Yes

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 8720169391956
- Net weight: 1.11 kg
- Gross weight: 1.19 kg
- Height: 20 cm
- Length: 12.5 cm
- Width: 15.5 cm



Issue date: 2026-05-13
Version: 0.136

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com