

PHILIPS

Filament Candle
Frosted 40W B35 E14

LED

2200-2700K

470lm

15000h

Dimming



8719514324299



Experience dimmable, warm white LED light

Philips LED frosted candles provide a soft, diffuse light effect and an exceptionally long life. With a pure and elegant design, this light bulb is the perfect match for chandelier fixtures with small (E14) fittings.

Choose for a sustainable solution

- Saves up to 90% Energy

Create the right light for your home

- Perfect for decorative fixtures

Highlights

Saves up to 90% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 90% in energy by replacing your existing incandescent or halogen bulbs

Perfect for decorative fixture



Modern lighting in Philips LED candles for use in decorative fixtures such as in chandeliers, ceiling fans, vanity strips, and post lights.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional candle
- Socket: E14
- Dimmable: Yes
- Bulb Finish: Frosted
- Bulb Material: Glass

Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Color rendering index (CRI): 90
- Color temperature: 2200–2700 K
- Nominal luminous flux: 470 lm
- Warm-up time to 60% light: 0.5
- Color Code: 922-927 | CCT of 2200K-2700K
- Luminous Efficacy (rated) (Nom): 138 lm/W

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable, WarmGlow

Packaging information

- EAN: 8719514324299
- EOC: 871951432429900
- Product title: LED classic 40W B35 E14 FR WGD90 SRT4

Power consumption

- Power factor: 0.6
- Voltage: 220–240 V
- Wattage equivalent: 40 W
- Energy Efficiency Label (EEL): D
- Power Consumption: 3.4 W
- Energy Consumption kWh/1000 h: 4

Product dimensions and weight

- Overall height: 97 mm
- Overall length: 97 mm
- Overall width: 35 mm

Technical specifications

- Frequency: 50–60
- EPREL Registration Number: 453269

Packaging dimensions and weight

- EAN/UPC - product: 8719514324299
- Net weight: 0.01 kg
- Gross weight: 0.03 kg
- Height: 14.6 cm
- Length: 4.6 cm
- Width: 6.3 cm



Issue date: 2025-08-06
Version: 0.380

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com