









Experience warm white LED light

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

High-quality light

Designed for the comfort of your eyes

Choose a simple replacement for your old lamps

· Similar shape and size as standard incandescent bulbs

Choose for a sustainable solution

· Long-life bulbs – Last up to 15 years

Highlights

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Replaces standard incandescents



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, energy-saving standard LED bulb. The perfect sustainable replacement for traditional standard incandescent bulbs.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Specifications

Bulb characteristics

· Intended use: Indoor

· Lamp shape: Non-directional bulb

Socket: B22Dimmable: NoLamp Finish: FrostedBulb material: Plastic

Durability

· Number of switch cycles: 50,000

· Nominal lifetime: 15,000

Environmental

• Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Light characteristics

• Beam angle: 150 degree(s)

· Colour rendering index (CRI): 80

· Colour temperature: 2700 K

· Nominal luminous flux: 470 lm

 Luminous efficacy (rated) (nom.): 111 lm/W

Miscellaneous

EveComfort: Yes

· LED innovations: EyeComfort

Packaging information

• EAN: 8720169324411

• EOC: 872016932441100

 Product title: LED 40W A60 B22 WW FR ND 2SRT6

Power consumption

• Power factor: 0.48

Voltage: AC 220-240 V

· Wattage equivalent: 40 W

· Energy efficiency label (EEL): E

• Power Consumption: 4.2 W

• Energy consumption kWh/1,000

hours: 5

Product dimensions and weight

Overall height: 105 mmOverall length: 105 mmOverall width: 60 mm

Technical specifications

• Frequency: 50-60

EPREL Registration Number: 1930250
Can it be used in closed luminaires: No

Packaging dimensions and weight

• EAN/UPC - product: 8720169324411

Net weight: 0.05 kgGross weight: 0.09 kgHeight: 14.6 cm

Length: 6.5 cmWidth: 13 cm



Issue date: 2025-09-17 Version: 0.203 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips