

# PHILIPS

Suspension light

myLiving

30899

chrome



30899/21/66



## Highlight your elegance

Create an air of elegance with this family of pendants. The metallized glass dome reflects and refracts light for a sparkling effect. Concealed dangling crystal drops that scatter light and captivate onlookers for a sheer luxurious feel.

### Ease of use

- Adjustable height to suit your needs

### Match your interior style

- Classical appeal

### Energy saving

- Designed for use with energy-saving light bulbs

### Premium quality

- Premium materials
- Carefully hand-crafted material

# Highlights

## Adjustable mounting



This product is delivered with long cables to offer you a maximum flexibility during installation. Choose the perfect height matching your needs.

## Classical appeal

Classical and antique design of this product is specially designed to suit your interiors

## Made for energy-saving bulbs



Philips energy-saving light bulbs conserve energy compared to traditional light sources, helping you to save money on your electricity bills and do your bit for the environment.

## Premium materials



Made of premium materials to assure the quality of the product.

## Hand-made materials

This product is made from a carefully hand-crafted materials to make sure its quality.

# Specifications

## Bulb characteristics

- Intended use: Indoor

## Design and finishing

- Color: Metallic Black
- Material: Glass, Crystals

## Extra feature/accessory incl.

- 4 light recipes: No
- 5 years warranty on the LED module: No
- Adjustable height: Yes
- Adjustable spot head: No
- Batteries included: No
- Bi-directional light beams: No
- Candle light effect: No
- Centerpiece: Yes
- Choose your color: No
- Clamp included: Yes
- Color changing (LED): No
- Day-and-night sensor: No
- Defined light beams: No
- Easy bulb swap: Yes
- Fully weatherproof: No
- Hue bridge included: No
- Hue Switch: No
- Hue Switch Included: No
- LED integrated: No

**Miscellaneous**

- Especially designed for: Living- & Bedroom
- Style: Historical
- Type: Suspension Lights
- EyeComfort: No

**Product dimensions and weight**

- Net weight: 4.330 kg
- Height maximum: 1,750 mm
- Height minimum: 220 mm
- Length: 40 cm
- Width: 40 cm

**Service**

- Warranty: 1 year(s)

**Technical specifications**

- Mains power: 230 V, 50-60 Hz
- Energy class included light source: no bulb included
- Fixture is compatible with bulb(s) of class: A++ to E
- Fitting/cap: E27
- Wattage bulb included: -
- Maximum wattage replacement bulb: 42
- IP code: IP20 | Finger-protected
- Class of protection: Class II – Double Insulated
- Number of light sources: 4

**Packaging dimensions and weight**

- EAN/UPC – product: 6947830420452
- Net weight: 4.33 kg
- Gross weight: 8 kg
- Height: 0 mm
- Length: 0 mm
- Width: 0 mm



Issue date: 2025-08-30  
Version: 0.666

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)