



# Superior light and style

The sleek Philips Spot Light COB Pro recessed spot in aluminium lies flat on your ceiling for a clean silhouette. Directable light enhances the decor

#### Designed for your living- and bedroom

· Create a stylish and welcoming atmosphere

### Match your interior

· Expressive and elegant form

#### Easy to experience

 Ideal for rooms with low ceilings, makes for an unobtrusive and subtle fixture.

### **Light effect**

- Bright and focused beam
- ${\boldsymbol{\cdot}}$  Durable synthetic diffuser for uniform light and reduced glare

#### **Premium quality**

• Durable and impact resistant die-cast aluminum housing

### Material & finishing

· Durable aluminum housing

### **Durability**

· Long life span up to 30,000 hours

# Highlights

#### Create a stylish atmosphere



This light is designed around the latest tastes, trends and lifestyles to blend effortlessly into your d?cor and define the localised ambiance you have always desired.

#### Expressive and elegant form

A clean, modern design provides elegance and sophistication to your rooms.

# Suitable for low ceilingsSlim design Bright and focused beam

Focus light on objects, a dining table or other interiors to draw attention to particular stylings.

# Durable synthetic diffuser for uniform light and reduced glare

Provides a soft glow for relaxation and focus without distracting glare.

# Durable and impact resistant die-cast aluminum housing

The die-cast aluminum housing of this item adds to a cultivated and refined contemporary atmosphere.

#### **Durable aluminum housing**

Creates a strong, clean and contemporary style for your space.

### Long life span up to 30,000 hours

Philips LED technology extends your product's lifetime up to 30,000 hours.

# Specifications

#### Design and finishing

Color: WhiteMaterial: Metal

#### **Durability**

· Nominal lifetime: 35,000

#### **Environmental**

• Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

# Extra feature/accessory incl.

- Adjustable spot head: Adjustable rise and fall
- · Dimmable with remote control: No
- · LED integrated: Yes
- · Remote control included: No

#### **Light characteristics**

Beam angle: 36 degree(s)Color rendering index (CRI): 80Color temperature: 4000 K

#### Miscellaneous

- · Especially designed for: Living Room
- EyeComfort: Yes

#### Product dimensions and weight

· Net weight: 0.206 kg

· Overall height: 50 mm

· Overall length: 90 mm

· Overall width: 90 mm

Recessed Ceiling cutout: 8.1 cm x 8.1 cm

#### **Service**

Warranty: 2 year(s)

#### **Technical specifications**

· Diameter: 90 mm

• Total lumen output fixture: 630

Light color: 4000

• Mains power: 220-240

· Fixture dimmable: No

· Wattage bulb included: 7

• IP code: IP20 | Finger-protected

Class of protection: Class II - Double
In sulption

Insulated

## Packaging dimensions and weight

• EAN/UPC - product: 8718696763001

Net weight: 0.14 kgGross weight: 0.16 kg

Height: 6.8 cmLength: 11 cmWidth: 10 cm



Issue date: 2025-12-01 Version: 0.320 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips