

# PHILIPS

## Downlight

Functional

HexaStyle

White

8719514437135



## The new Shape of Style

Reimagine your world with Philips HexaStyle downlights, which have a unique hexagonal shape with a round fitment for easy installation. These downlights give you the freedom to embrace your creativity by arranging them in any pattern and configuration, and design your space your way!

### Match your interior

- Expressive and elegant form
- Super slim design

### Mounting

- Patterned installation design

### Durability

- Long life span up to 25,000 hours

# Highlights

## Expressive and elegant form

A clean, modern design provides elegance and sophistication to your rooms.

## Super slim design

Slim design is ideal for low-ceiling rooms, sitting flush against the surface.

## Patterned installation design

Attractive and memorable installation design with eye-catching pattern.

## Long life span up to 25,000 hours

Philips LED technology extends your product's lifetime up to 25,000 hours

# Specifications

## Bulb characteristics

- Dimmable: No

## Design and finishing

- Color: White
- Material: Plastic

## Durability

- Nominal lifetime: 25,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Beam angle: 120 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 3000 K

## Miscellaneous

- EyeComfort: Yes

## Product dimensions and weight

- Net weight: 0.09 kg
- Overall height: 21 mm
- Overall length: 127 mm
- Overall width: 116 mm
- Recessed Ceiling cutout: 10.0 cm x 10.0 cm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Diameter: 127 mm
- Total lumen output fixture: 800
- Light color: 3000
- Mains power: 220-240
- Wattage bulb included: 8
- IP code: IP20 | Finger-protected
- Class of protection: Class II - Double Insulated

## Packaging dimensions and weight

- EAN/UPC - product: 8719514437135
- Net weight: 0.09 kg
- Gross weight: 0.16 kg
- Height: 4.5 cm
- Length: 18.7 cm
- Width: 16 cm



Issue date: 2025-09-03  
Version: 0.105

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)