



1 x 27CC/LED/840 929002395600**1 x 3700 lm****Polar intensity diagram**

Light output ratio 1.00
 Service upward 0.48
 Service downward 0.52


CIE flux code 16 41 70 52 100

UGRcen (4Hx8H, 0.25H) 27

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80 0.80				0.70 0.70				0.50 0.50			
	0.80	0.50	0.30	0.10	0.70	0.50	0.30	0.10	0.50	0.30	0.10	0.00
0.60	0.32	0.31	0.30	0.29	0.28	0.21	0.17	0.13	0.14	0.10	0.05	0.00
0.80	0.41	0.39	0.38	0.37	0.36	0.28	0.23	0.18	0.18	0.14	0.08	0.00
1.00	0.49	0.45	0.44	0.43	0.41	0.33	0.28	0.23	0.22	0.18	0.10	0.00
1.25	0.56	0.51	0.51	0.49	0.47	0.39	0.33	0.27	0.26	0.22	0.13	0.00
1.50	0.62	0.56	0.56	0.54	0.52	0.44	0.37	0.32	0.30	0.26	0.16	0.00
2.00	0.71	0.63	0.64	0.61	0.58	0.51	0.43	0.38	0.35	0.31	0.20	0.00
2.50	0.77	0.68	0.70	0.66	0.63	0.56	0.48	0.43	0.39	0.36	0.24	0.00
3.00	0.82	0.72	0.75	0.70	0.66	0.60	0.51	0.47	0.42	0.39	0.26	0.00
4.00	0.89	0.77	0.81	0.76	0.71	0.66	0.56	0.52	0.47	0.44	0.30	0.00
5.00	0.93	0.80	0.85	0.79	0.74	0.70	0.59	0.56	0.50	0.47	0.33	0.00

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	8820	10656	9636	9868	7959	10594	10414
50.0	9912	11930	10823	11009	8812	11813	11797
55.0	11010	13251	12030	12220	9706	13131	13285
60.0	12197	14564	13111	13359	10615	14421	14729
65.0	13385	15848	14163	14487	11462	15734	16170
70.0	14931	17504	15496	15827	12534	17337	18046
75.0	17171	19695	17273	17627	14068	19437	20613
80.0	20086	22595	19609	19917	15948	22251	24132
85.0	24320	26543	22753	23007	18587	26198	29149
90.0	30633	32127	27087	27228	22177	31732	36620

(cd/m²)

2019-12-20