


1 x Tforce HB GC Entry THD 3600lm


1 x 3600 lm

Polar intensity diagram

Light output ratio 1.00
 Service upward 0.26
 Service downward 0.74


CIE flux code 31 58 82 74 100

UGRcen (4Hx8H, 0.25H) 27

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.80	0.50	0.30	0.10	0.30	0.20	0.10	0.10	0.10	0.10	0.00	0.00
0.80	0.47	0.44	0.45	0.44	0.42	0.34	0.32	0.26	0.29	0.24	0.20	0.15
1.00	0.55	0.51	0.52	0.50	0.49	0.41	0.37	0.32	0.34	0.29	0.24	0.20
1.25	0.63	0.58	0.59	0.57	0.55	0.47	0.43	0.38	0.39	0.35	0.29	0.24
1.50	0.69	0.63	0.65	0.62	0.60	0.52	0.48	0.42	0.43	0.39	0.33	0.29
2.00	0.78	0.70	0.74	0.70	0.67	0.60	0.55	0.50	0.50	0.46	0.39	0.33
2.50	0.85	0.75	0.80	0.76	0.72	0.66	0.60	0.56	0.55	0.51	0.43	0.39
3.00	0.90	0.79	0.85	0.80	0.75	0.70	0.64	0.60	0.58	0.55	0.47	0.43
4.00	0.97	0.84	0.91	0.85	0.80	0.75	0.69	0.65	0.63	0.60	0.52	0.47
5.00	1.01	0.87	0.95	0.88	0.83	0.79	0.72	0.69	0.66	0.64	0.55	0.52

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	25715	22544	20937	20461	21000	22664	25890
50.0	24273	21126	19551	19091	19624	21261	24468
55.0	22962	19823	18272	17824	18338	19940	23121
60.0	21687	18583	17066	16628	17118	18691	21863
65.0	20497	17444	15965	15537	16024	17563	20690
70.0	19431	16408	14960	14541	15009	16500	19564
75.0	18456	15470	14049	13632	14074	15534	18586
80.0	17560	14599	13204	12791	13231	14648	17627
85.0	16771	13825	12452	12048	12464	13854	16827
90.0	16065	13137	11786	11382	11792	13158	16118

(cd/m²)

LTC

2022-09-30