



1 x 36CC/LED/850 929002999100**1 x 5400 lm****Polar intensity diagram**

Light output ratio 1.00
 Service upward 0.46
 Service downward 0.54


CIE flux code 18 43 71 54 100

UGRcen (4Hx8H, 0.25H) 26

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80 0.80				0.70 0.70				0.50 0.50			
	0.80	0.50	0.30	0.10	0.70	0.50	0.30	0.10	0.50	0.30	0.10	0.00
0.60	0.33	0.31	0.30	0.30	0.29	0.21	0.18	0.14	0.15	0.11	0.06	0.00
0.80	0.42	0.39	0.38	0.37	0.36	0.28	0.24	0.19	0.19	0.15	0.09	0.00
1.00	0.49	0.46	0.45	0.43	0.42	0.34	0.29	0.23	0.23	0.19	0.12	0.00
1.25	0.57	0.52	0.52	0.50	0.48	0.40	0.34	0.28	0.28	0.23	0.15	0.00
1.50	0.62	0.57	0.57	0.55	0.52	0.45	0.38	0.33	0.31	0.27	0.17	0.00
2.00	0.71	0.64	0.65	0.62	0.59	0.52	0.44	0.39	0.37	0.33	0.22	0.00
2.50	0.78	0.69	0.71	0.67	0.64	0.57	0.49	0.44	0.41	0.37	0.25	0.00
3.00	0.83	0.72	0.75	0.71	0.67	0.61	0.52	0.48	0.44	0.40	0.28	0.00
4.00	0.89	0.77	0.81	0.76	0.72	0.67	0.57	0.53	0.48	0.45	0.32	0.00
5.00	0.94	0.81	0.85	0.80	0.75	0.70	0.60	0.57	0.51	0.48	0.35	0.00

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	9655	9006	8607	8584	8775	9039	9495
50.0	10395	9640	9188	9162	9357	9713	10268
55.0	11245	10332	9777	9747	10004	10411	11053
60.0	12359	11263	10565	10510	10793	11299	12091
65.0	13781	12421	11600	11497	11829	12450	13512
70.0	15584	13838	12819	12721	13131	13893	15259
75.0	17595	15380	14088	13999	14508	15499	17232
80.0	20118	17301	15667	15549	16205	17410	19741
85.0	23787	19878	17795	17624	18424	20091	23319
90.0	29156	23626	20827	20532	21540	23870	28654

(cd/m²)

2021-06-03