



1 x Tforce SOX 929002496900**1 x 4000 lm****Polar intensity diagram**

Light output ratio 1.00
 Service upward 0.22
 Service downward 0.78


CIE flux code 33 60 82 78 100

UGRcen (4Hx8H, 0.25H) 29

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.39	0.37	0.37	0.37	0.36	0.28	0.26	0.21	0.24	0.20	0.17	0.17
0.80	0.48	0.46	0.46	0.45	0.44	0.36	0.33	0.28	0.31	0.26	0.22	0.22
1.00	0.56	0.52	0.54	0.52	0.50	0.42	0.39	0.34	0.36	0.31	0.27	0.27
1.25	0.64	0.59	0.61	0.58	0.56	0.48	0.45	0.40	0.41	0.37	0.31	0.31
1.50	0.70	0.64	0.67	0.64	0.61	0.53	0.50	0.44	0.46	0.41	0.35	0.35
2.00	0.80	0.71	0.75	0.72	0.68	0.61	0.57	0.52	0.53	0.48	0.42	0.42
2.50	0.86	0.76	0.81	0.77	0.73	0.67	0.62	0.57	0.57	0.53	0.46	0.46
3.00	0.91	0.80	0.86	0.81	0.76	0.71	0.66	0.62	0.61	0.57	0.50	0.50
4.00	0.98	0.84	0.92	0.86	0.81	0.76	0.71	0.67	0.66	0.62	0.55	0.55
5.00	1.02	0.87	0.96	0.90	0.84	0.80	0.74	0.71	0.69	0.66	0.58	0.58

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	22227	21571	21141	20858	21086	22698	26362
50.0	22066	21309	20732	20226	20105	21456	25110
55.0	22019	21168	20432	19665	19184	20148	23479
60.0	22126	21132	20224	19212	18274	18866	22121
65.0	22174	21136	20133	18935	17510	17479	19961
70.0	22516	21335	20180	18775	16917	16144	17258
75.0	22778	21488	20257	18777	16471	14814	13871
80.0	23207	21797	20460	18837	16158	13667	10174
85.0	23494	22079	20711	18980	15996	12574	4638
90.0	23929	22381	20985	19305	15968	12213	947

(cd/m²)

2020-12-18