



1 x 9290020250 A60 2700K 2.2W

1 x 250 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.00
Service upward 0.50
Service downward 0.50

CIE flux code 14 38 68 50 100

UGRcen (4Hx8H, 0.25H) 23

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)															
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.80	0.80	0.70	0.70	0.70
0.60	0.30	0.10	0.30	0.20	0.10	0.10	0.10	0.10	0.10	0.10	0.00	0.30	0.10	0.30	0.20	0.10
0.80	0.41	0.38	0.37	0.36	0.35	0.27	0.22	0.17	0.17	0.13	0.04	0.41	0.38	0.37	0.36	0.35
1.00	0.48	0.44	0.43	0.42	0.41	0.33	0.27	0.22	0.21	0.17	0.09	0.48	0.44	0.43	0.42	0.41
1.25	0.55	0.51	0.50	0.48	0.46	0.38	0.32	0.26	0.25	0.21	0.12	0.55	0.51	0.50	0.48	0.46
1.50	0.61	0.55	0.55	0.53	0.51	0.43	0.36	0.30	0.29	0.24	0.14	0.61	0.55	0.55	0.53	0.51
2.00	0.70	0.63	0.63	0.60	0.57	0.50	0.42	0.37	0.34	0.30	0.18	0.70	0.63	0.63	0.60	0.57
2.50	0.76	0.67	0.69	0.65	0.62	0.55	0.46	0.42	0.38	0.34	0.22	0.76	0.67	0.69	0.65	0.62
3.00	0.81	0.71	0.74	0.69	0.65	0.59	0.50	0.46	0.41	0.37	0.24	0.81	0.71	0.74	0.69	0.65
4.00	0.88	0.76	0.80	0.75	0.70	0.65	0.55	0.51	0.45	0.42	0.28	0.88	0.76	0.80	0.75	0.70
5.00	0.92	0.79	0.84	0.78	0.73	0.69	0.58	0.55	0.48	0.45	0.31	0.92	0.79	0.84	0.78	0.73

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	3848	3492	3299	3239	3299	3492	3848
50.0	4269	3839	3611	3539	3611	3839	4269
55.0	4655	4148	3882	3799	3882	4148	4655
60.0	5043	4452	4147	4052	4147	4452	5043
65.0	5497	4805	4452	4344	4452	4805	5497
70.0	5967	5160	4756	4632	4756	5160	5967
75.0	6513	5566	5100	4958	5100	5566	6513
80.0	7118	6004	5467	5305	5467	6004	7118
85.0	7849	6522	5896	5709	5896	6522	7849
90.0	8710	7112	6376	6159	6376	7112	8710

(cd/m²)

2019-02-26