




Candle 40W 2700K E27P45 9290013457

1 x 470 lm

Polar intensity diagram**Quantity estimation diagram****UGR diagram**

Light output ratio 1.00
Service upward 0.49
Service downward 0.51

CIE flux code 9 35 66 51 100

UGRcen (4Hx8H, 0.25H) 26

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)															
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.80	0.80	0.70	0.70	0.70
0.50	0.50	0.50	0.50	0.50	0.50	0.30	0.30	0.10	0.00	0.00	0.00	0.50	0.50	0.50	0.50	0.30
0.30	0.10	0.30	0.20	0.10	0.10	0.10	0.10	0.10	0.10	0.00	0.00	0.10	0.10	0.10	0.10	0.00
0.60	0.30	0.29	0.27	0.27	0.26	0.18	0.15	0.10	0.11	0.07	0.02	0.30	0.29	0.27	0.26	0.18
0.80	0.39	0.37	0.35	0.34	0.33	0.25	0.20	0.15	0.16	0.12	0.05	0.39	0.37	0.35	0.34	0.25
1.00	0.46	0.43	0.42	0.40	0.39	0.31	0.25	0.20	0.20	0.15	0.07	0.46	0.43	0.42	0.40	0.31
1.25	0.54	0.49	0.49	0.47	0.45	0.37	0.30	0.25	0.24	0.19	0.10	0.54	0.49	0.49	0.47	0.37
1.50	0.60	0.54	0.54	0.52	0.50	0.41	0.34	0.29	0.27	0.23	0.13	0.60	0.54	0.54	0.52	0.41
2.00	0.69	0.61	0.62	0.59	0.56	0.49	0.41	0.35	0.33	0.29	0.17	0.69	0.61	0.62	0.59	0.49
2.50	0.75	0.66	0.68	0.64	0.61	0.54	0.45	0.40	0.37	0.33	0.20	0.75	0.66	0.68	0.64	0.54
3.00	0.80	0.70	0.72	0.68	0.65	0.58	0.49	0.44	0.40	0.36	0.23	0.80	0.70	0.72	0.68	0.58
4.00	0.87	0.75	0.79	0.74	0.69	0.64	0.54	0.50	0.44	0.41	0.27	0.87	0.75	0.79	0.74	0.64
5.00	0.92	0.79	0.83	0.77	0.73	0.68	0.57	0.54	0.47	0.44	0.30	0.92	0.79	0.83	0.77	0.68

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	9317	9317	9317	9317	9317	9317	9317
50.0	10063	10063	10063	10063	10063	10063	10063
55.0	10760	10760	10760	10760	10760	10760	10760
60.0	11386	11386	11386	11386	11386	11386	11386
65.0	11962	11962	11962	11962	11962	11962	11962
70.0	12489	12489	12489	12489	12489	12489	12489
75.0	12970	12970	12970	12970	12970	12970	12970
80.0	13423	13423	13423	13423	13423	13423	13423
85.0	13841	13841	13841	13841	13841	13841	13841
90.0	14233	14233	14233	14233	14233	14233	14233

(cd/m²)

SL24964-2

2017-03-02