


1 x 9290023336 E26 A19 8.8W 2700K

1 x 800 lm

Polar intensity diagram




Light output ratio 1.00
 Service upward 0.32
 Service downward 0.68

CIE flux code 29 56 79 68 100

UGRcen (4Hx8H, 0.25H) 25

Quantity estimation diagram




Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)															
	0.80				0.70				0.50				0.30			
	0.80	0.80	0.50	0.50	0.50	0.50	0.50	0.30	0.30	0.30	0.30	0.10	0.10	0.10	0.10	0.00
0.60	0.37	0.35	0.35	0.34	0.33	0.26	0.23	0.18	0.21	0.17	0.12					
0.80	0.46	0.43	0.43	0.42	0.41	0.33	0.30	0.25	0.26	0.22	0.17					
1.00	0.54	0.50	0.50	0.49	0.47	0.39	0.35	0.30	0.31	0.27	0.21					
1.25	0.61	0.56	0.58	0.55	0.53	0.45	0.41	0.36	0.36	0.32	0.25					
1.50	0.68	0.61	0.63	0.60	0.58	0.50	0.45	0.40	0.40	0.36	0.29					
2.00	0.77	0.69	0.72	0.68	0.65	0.58	0.52	0.47	0.46	0.42	0.34					
2.50	0.83	0.73	0.78	0.73	0.70	0.63	0.57	0.52	0.51	0.47	0.38					
3.00	0.88	0.77	0.82	0.77	0.73	0.67	0.61	0.56	0.54	0.51	0.41					
4.00	0.94	0.82	0.88	0.82	0.78	0.73	0.65	0.62	0.59	0.56	0.46					
5.00	0.99	0.85	0.92	0.86	0.81	0.76	0.69	0.66	0.62	0.59	0.49					

Ceiling mounted

UGR diagram



Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	12548	10971	10168	9920	10168	10971	12548
50.0	11992	10404	9605	9360	9605	10404	11992
55.0	11502	9906	9111	8868	9111	9906	11502
60.0	11096	9487	8695	8454	8695	9487	11096
65.0	10727	9106	8316	8078	8316	9106	10727
70.0	10412	8776	7987	7749	7987	8776	10412
75.0	10150	8492	7701	7464	7701	8492	10150
80.0	9938	8251	7456	7218	7456	8251	9938
85.0	9757	8036	7234	6996	7234	8036	9757
90.0	9638	7869	7055	6815	7055	7869	9638

(cd/m²)

2019-11-20