


1 x 9290024128 7.2W 2700K

1 x 650 lm

Polar intensity diagram




Light output ratio 1.00
Service upward 0.44
Service downward 0.56

CIE flux code 16 42 70 56 100

UGRcen (4Hx8H, 0.25H) 27

Quantity estimation diagram




Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.30	0.10	0.30	0.20	0.10	0.10	0.10	0.10	0.10	0.10	0.00	0.00
0.80	0.41	0.39	0.38	0.37	0.36	0.27	0.23	0.18	0.19	0.15	0.08	
1.00	0.48	0.45	0.44	0.43	0.41	0.33	0.28	0.23	0.23	0.19	0.11	
1.25	0.56	0.51	0.51	0.49	0.47	0.39	0.33	0.28	0.27	0.23	0.14	
1.50	0.62	0.56	0.57	0.54	0.52	0.44	0.37	0.32	0.31	0.27	0.17	
2.00	0.71	0.63	0.65	0.62	0.59	0.51	0.44	0.39	0.37	0.32	0.22	
2.50	0.77	0.68	0.71	0.67	0.63	0.57	0.48	0.44	0.41	0.37	0.25	
3.00	0.82	0.72	0.75	0.71	0.67	0.61	0.52	0.48	0.44	0.40	0.28	
4.00	0.89	0.77	0.81	0.76	0.72	0.66	0.57	0.53	0.48	0.45	0.32	
5.00	0.94	0.80	0.85	0.80	0.75	0.70	0.60	0.57	0.51	0.48	0.35	

Ceiling mounted

UGR diagram



Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	11907	10664	9955	9659	9733	10193	11126
50.0	12685	11277	10494	10182	10292	10847	11966
55.0	13500	11904	11033	10699	10839	11488	12799
60.0	14371	12567	11604	11248	11425	12182	13716
65.0	15341	13300	12234	11854	12075	12957	14752
70.0	16538	14181	12971	12543	12792	13794	15866
75.0	17755	15052	13690	13218	13506	14649	17045
80.0	19063	15964	14437	13919	14256	15568	18357
85.0	20500	16931	15216	14650	15046	16556	19822
90.0	22346	18140	16169	15527	15980	17718	21571

(cd/m²)

2020-06-03