



1 x 9290035848 A60-8 8W 120V 3000K**1 x 800 lm****Polar intensity diagram**

Light output ratio 0.97
 Service upward 0.34
 Service downward 0.63


CIE flux code 27 54 78 65 97

UGRcen (4Hx8H, 0.25H) 28

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80 0.80				0.70 0.70				0.50 0.50			
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.35	0.33	0.33	0.32	0.31	0.24	0.21	0.17	0.19	0.15	0.11	0.11
0.80	0.44	0.41	0.41	0.40	0.39	0.31	0.28	0.23	0.24	0.20	0.15	0.15
1.00	0.51	0.48	0.48	0.46	0.45	0.37	0.33	0.28	0.29	0.24	0.18	0.18
1.25	0.59	0.54	0.55	0.52	0.51	0.43	0.38	0.33	0.33	0.29	0.22	0.22
1.50	0.65	0.59	0.60	0.57	0.55	0.48	0.42	0.37	0.37	0.33	0.25	0.25
2.00	0.73	0.66	0.68	0.65	0.62	0.55	0.49	0.44	0.43	0.39	0.31	0.31
2.50	0.80	0.70	0.74	0.70	0.66	0.60	0.54	0.49	0.47	0.44	0.35	0.35
3.00	0.84	0.74	0.78	0.74	0.70	0.64	0.57	0.53	0.50	0.47	0.37	0.37
4.00	0.91	0.78	0.84	0.79	0.74	0.69	0.62	0.58	0.55	0.52	0.42	0.42
5.00	0.95	0.82	0.88	0.82	0.77	0.73	0.65	0.62	0.58	0.55	0.44	0.44

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	24674	22192	20755	20131	20227	21056	22745
50.0	24867	22128	20568	19897	19999	20893	22732
55.0	25176	22154	20464	19743	19853	20814	22815
60.0	25618	22279	20446	19671	19788	20824	23003
65.0	26226	22521	20525	19690	19816	20934	23316
70.0	26985	22851	20672	19770	19906	21116	23729
75.0	27985	23331	20935	19954	20102	21420	24307
80.0	29293	23988	21330	20255	20417	21864	25085
85.0	31017	24869	21884	20695	20874	22479	26119
90.0	33319	26037	22634	21301	21500	23306	27488

(cd/m²)

2022-11-03