



1 x 9290035849 A60-8 8W 120V 4000K**1 x 800 lm****Polar intensity diagram**

Light output ratio 1.00
 Service upward 0.36
 Service downward 0.64


CIE flux code 27 53 78 64 100

UGRcen (4Hx8H, 0.25H) 28

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80 0.80				0.70 0.70				0.50 0.50			
	0.80	0.50	0.30	0.10	0.80	0.50	0.30	0.10	0.80	0.50	0.30	0.10
0.60	0.36	0.34	0.34	0.33	0.32	0.25	0.22	0.17	0.19	0.15	0.11	0.00
0.80	0.45	0.42	0.42	0.41	0.40	0.32	0.28	0.23	0.25	0.20	0.15	0.00
1.00	0.53	0.49	0.49	0.47	0.46	0.38	0.34	0.28	0.29	0.25	0.19	0.00
1.25	0.60	0.55	0.56	0.54	0.52	0.44	0.39	0.34	0.34	0.30	0.22	0.00
1.50	0.66	0.60	0.62	0.59	0.57	0.49	0.43	0.38	0.38	0.34	0.26	0.00
2.00	0.75	0.67	0.70	0.67	0.63	0.57	0.50	0.45	0.44	0.40	0.31	0.00
2.50	0.82	0.72	0.76	0.72	0.68	0.62	0.55	0.50	0.48	0.45	0.35	0.00
3.00	0.87	0.76	0.80	0.76	0.72	0.66	0.59	0.54	0.52	0.48	0.38	0.00
4.00	0.93	0.81	0.86	0.81	0.76	0.71	0.64	0.60	0.56	0.53	0.42	0.00
5.00	0.98	0.84	0.90	0.85	0.79	0.75	0.67	0.64	0.59	0.56	0.45	0.00

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	23807	21259	19801	19172	19268	20105	21823
50.0	23914	21125	19556	18885	18987	19882	21737
55.0	24139	21089	19402	18687	18795	19751	21753
60.0	24510	21166	19349	18585	18701	19722	21887
65.0	24996	21320	19360	18544	18668	19761	22105
70.0	25626	21566	19445	18571	18703	19876	22423
75.0	26471	21949	19640	18698	18840	20107	22893
80.0	27568	22479	19945	18924	19077	20453	23527
85.0	28991	23185	20377	19260	19427	20936	24363
90.0	30853	24110	20958	19724	19908	21581	25453

(cd/m²)

2022-11-03