



1 x 9290030039 13W 3000K**1 x 1521 lm****Polar intensity diagram**

Light output ratio 1.00
 Service upward 0.23
 Service downward 0.77


CIE flux code 33 61 83 77 100

UGRcen (4Hx8H, 0.25H) 31

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.39	0.37	0.37	0.36	0.35	0.28	0.26	0.21	0.24	0.20	0.16	0.16
0.80	0.48	0.46	0.46	0.45	0.44	0.36	0.33	0.28	0.30	0.26	0.22	0.22
1.00	0.56	0.52	0.54	0.52	0.50	0.42	0.39	0.34	0.36	0.31	0.26	0.26
1.25	0.64	0.59	0.61	0.59	0.56	0.49	0.45	0.40	0.41	0.37	0.31	0.31
1.50	0.70	0.64	0.67	0.64	0.61	0.54	0.50	0.44	0.46	0.41	0.35	0.35
2.00	0.80	0.71	0.75	0.72	0.68	0.62	0.57	0.52	0.53	0.49	0.42	0.42
2.50	0.86	0.76	0.82	0.77	0.73	0.67	0.62	0.58	0.57	0.54	0.46	0.46
3.00	0.91	0.80	0.86	0.81	0.77	0.71	0.66	0.62	0.61	0.57	0.50	0.50
4.00	0.98	0.85	0.92	0.86	0.81	0.77	0.71	0.67	0.65	0.63	0.55	0.55
5.00	1.02	0.88	0.96	0.90	0.84	0.80	0.74	0.71	0.69	0.66	0.58	0.58

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	66107	59101	55010	53144	53217	55238	59522
50.0	64161	56720	52450	50521	50596	52686	57161
55.0	62466	54578	50135	48147	48223	50379	55041
60.0	60697	52379	47783	45747	45825	48034	52861
65.0	60083	51162	46333	44217	44298	46595	51673
70.0	57958	48635	43702	41563	41645	43968	49162
75.0	57243	47255	42099	39891	39976	42374	47810
80.0	56162	45499	40149	37890	37976	40433	46082
85.0	56519	44787	39091	36723	36813	39390	45415
90.0	58293	44967	38750	36211	36307	39072	45663

(cd/m²)

2021-06-02