



**1 x 9290030063 6W 3000K**

1 x 600 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.00  
Service upward 0.38  
Service downward 0.62

CIE flux code 28 54 78 62 100

UGRcen (4Hx8H, 0.25H) 27

Utilisation factor table

| Room Index k | Reflectances (%) for ceiling, walls and working plane (CIE) |      |      |      |      |      |      |      |      |      |      |      |      |      |      |      |
|--------------|-------------------------------------------------------------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|
|              | 0.80                                                        | 0.80 | 0.70 | 0.70 | 0.70 | 0.70 | 0.50 | 0.50 | 0.30 | 0.30 | 0.00 | 0.80 | 0.80 | 0.70 | 0.70 | 0.70 |
| 0.60         | 0.36                                                        | 0.35 | 0.34 | 0.33 | 0.33 | 0.25 | 0.22 | 0.18 | 0.19 | 0.16 | 0.11 | 0.36 | 0.35 | 0.34 | 0.33 | 0.25 |
| 0.80         | 0.46                                                        | 0.43 | 0.42 | 0.41 | 0.40 | 0.32 | 0.28 | 0.24 | 0.25 | 0.21 | 0.15 | 0.46 | 0.43 | 0.42 | 0.41 | 0.32 |
| 1.00         | 0.53                                                        | 0.49 | 0.49 | 0.48 | 0.46 | 0.38 | 0.34 | 0.29 | 0.29 | 0.25 | 0.18 | 0.53 | 0.49 | 0.49 | 0.48 | 0.38 |
| 1.25         | 0.61                                                        | 0.56 | 0.56 | 0.54 | 0.52 | 0.44 | 0.39 | 0.34 | 0.34 | 0.30 | 0.22 | 0.61 | 0.56 | 0.56 | 0.54 | 0.44 |
| 1.50         | 0.67                                                        | 0.60 | 0.62 | 0.59 | 0.57 | 0.49 | 0.43 | 0.38 | 0.38 | 0.34 | 0.25 | 0.67 | 0.60 | 0.62 | 0.59 | 0.49 |
| 2.00         | 0.76                                                        | 0.68 | 0.70 | 0.67 | 0.63 | 0.57 | 0.50 | 0.45 | 0.44 | 0.40 | 0.30 | 0.76 | 0.68 | 0.70 | 0.67 | 0.57 |
| 2.50         | 0.82                                                        | 0.72 | 0.76 | 0.72 | 0.68 | 0.62 | 0.55 | 0.50 | 0.48 | 0.44 | 0.34 | 0.82 | 0.72 | 0.76 | 0.72 | 0.62 |
| 3.00         | 0.87                                                        | 0.76 | 0.80 | 0.76 | 0.71 | 0.66 | 0.58 | 0.54 | 0.51 | 0.48 | 0.37 | 0.87 | 0.76 | 0.80 | 0.76 | 0.66 |
| 4.00         | 0.93                                                        | 0.81 | 0.86 | 0.81 | 0.76 | 0.71 | 0.63 | 0.59 | 0.55 | 0.52 | 0.41 | 0.93 | 0.81 | 0.86 | 0.81 | 0.71 |
| 5.00         | 0.98                                                        | 0.84 | 0.90 | 0.84 | 0.79 | 0.75 | 0.66 | 0.63 | 0.58 | 0.56 | 0.44 | 0.98 | 0.84 | 0.90 | 0.84 | 0.75 |

Ceiling mounted

Luminance Table

| Plane Cone | 0.0   | 15.0  | 30.0  | 45.0  | 60.0  | 75.0  | 90.0  |
|------------|-------|-------|-------|-------|-------|-------|-------|
| 45.0       | 17213 | 15707 | 14840 | 14492 | 14618 | 15234 | 16423 |
| 50.0       | 17371 | 15697 | 14747 | 14369 | 14506 | 15178 | 16488 |
| 55.0       | 17613 | 15752 | 14714 | 14304 | 14452 | 15183 | 16628 |
| 60.0       | 17984 | 15907 | 14768 | 14322 | 14482 | 15281 | 16878 |
| 65.0       | 18486 | 16155 | 14900 | 14413 | 14588 | 15463 | 17238 |
| 70.0       | 19139 | 16502 | 15112 | 14577 | 14769 | 15733 | 17718 |
| 75.0       | 20050 | 17026 | 15467 | 14875 | 15087 | 16161 | 18409 |
| 80.0       | 21289 | 17758 | 15986 | 15322 | 15559 | 16770 | 19357 |
| 85.0       | 22920 | 18711 | 16666 | 15910 | 16180 | 17566 | 20595 |
| 90.0       | 25204 | 20030 | 17615 | 16737 | 17049 | 18670 | 22311 |

(cd/m²)

2021-06-02