



1 x 9290023053 6500K 13W E27A60

1 x 1450 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.00
Service upward 0.20
Service downward 0.80

CIE flux code 35 63 85 80 100

UGRcen (4Hx8H, 0.25H) 29

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)															
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.80	0.80	0.70	0.70	0.70
0.60	0.40	0.38	0.38	0.38	0.37	0.29	0.27	0.23	0.26	0.21	0.18	0.40	0.38	0.38	0.37	0.29
0.80	0.50	0.47	0.48	0.46	0.45	0.37	0.35	0.29	0.32	0.28	0.24	0.50	0.47	0.48	0.46	0.37
1.00	0.58	0.54	0.55	0.53	0.51	0.43	0.41	0.35	0.38	0.33	0.29	0.58	0.54	0.55	0.53	0.43
1.25	0.66	0.60	0.62	0.60	0.58	0.50	0.47	0.42	0.44	0.39	0.34	0.66	0.60	0.62	0.60	0.50
1.50	0.72	0.65	0.68	0.65	0.63	0.55	0.52	0.46	0.48	0.44	0.38	0.72	0.65	0.68	0.65	0.55
2.00	0.81	0.73	0.77	0.73	0.70	0.63	0.59	0.54	0.55	0.51	0.45	0.81	0.73	0.77	0.73	0.63
2.50	0.88	0.78	0.83	0.79	0.75	0.69	0.64	0.60	0.60	0.56	0.50	0.88	0.78	0.83	0.79	0.69
3.00	0.93	0.81	0.88	0.83	0.78	0.73	0.68	0.64	0.64	0.60	0.53	0.93	0.81	0.88	0.83	0.73
4.00	0.99	0.86	0.94	0.88	0.83	0.78	0.73	0.70	0.68	0.65	0.58	0.99	0.86	0.94	0.88	0.78
5.00	1.04	0.89	0.98	0.91	0.86	0.82	0.77	0.74	0.71	0.69	0.61	1.04	0.89	0.98	0.91	0.82

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	48165	43700	41294	40533	41294	43700	48165
50.0	45720	41116	38668	37898	38668	41116	45720
55.0	43524	38787	36303	35527	36303	38787	43524
60.0	41143	36321	33829	33055	33829	36321	41143
65.0	38907	34007	31512	30742	31512	34007	38907
70.0	36868	31881	29383	28618	29383	31881	36868
75.0	35101	29999	27488	26725	27488	29999	35101
80.0	33515	28271	25739	24976	25739	28271	33515
85.0	32332	26867	24287	23516	24287	26867	32332
90.0	31493	25714	23055	22269	23055	25714	31493

(cd/m²)

2019-12-26