



1 x 9290024284 16W 6500K

1 x 2300 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.00
Service upward 0.16
Service downward 0.84

CIE flux code 36 65 86 84 100

UGRcen (4Hx8H, 0.25H) 30

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80				0.70				0.50			
	0.80	0.50	0.30	0.10	0.80	0.50	0.30	0.10	0.80	0.50	0.30	0.10
0.60	0.41	0.39	0.39	0.38	0.37	0.30	0.28	0.23	0.27	0.22	0.19	
0.80	0.51	0.47	0.49	0.47	0.46	0.38	0.36	0.31	0.34	0.29	0.26	
1.00	0.59	0.54	0.56	0.54	0.53	0.45	0.42	0.37	0.40	0.35	0.31	
1.25	0.67	0.61	0.64	0.61	0.59	0.51	0.49	0.43	0.46	0.41	0.37	
1.50	0.73	0.66	0.70	0.67	0.64	0.57	0.54	0.48	0.50	0.46	0.41	
2.00	0.83	0.74	0.79	0.75	0.71	0.65	0.61	0.56	0.58	0.54	0.48	
2.50	0.89	0.79	0.85	0.80	0.76	0.70	0.66	0.62	0.63	0.59	0.53	
3.00	0.94	0.82	0.90	0.84	0.80	0.74	0.70	0.66	0.66	0.63	0.57	
4.00	1.01	0.87	0.96	0.90	0.84	0.80	0.75	0.72	0.71	0.68	0.62	
5.00	1.05	0.90	1.00	0.93	0.87	0.83	0.79	0.76	0.74	0.72	0.65	

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	58639	51345	47208	45335	45369	47316	51550
50.0	55332	47899	43757	41899	41933	43864	48105
55.0	51982	44480	40374	38550	38583	40480	44685
60.0	48449	40965	36944	35174	35206	37048	41168
65.0	44774	37388	33495	31798	31829	33595	37586
70.0	41229	33974	30227	28609	28638	30322	34166
75.0	37769	30679	27095	25565	25592	27186	30864
80.0	34582	27649	24226	22781	22807	24312	27827
85.0	31768	24949	21672	20304	20328	21753	25121
90.0	29304	22543	19391	18094	18117	19469	22710

(cd/m²)

2020-12-02