



1 x 9290030955 6W 6500K**1 x 620 lm****Polar intensity diagram**

Light output ratio 1.00
 Service upward 0.35
 Service downward 0.65


CIE flux code 22 49 75 65 100

UGRcen (4Hx8H, 0.25H) 29

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.34	0.32	0.32	0.31	0.30	0.23	0.20	0.15	0.17	0.13	0.09	0.09
0.80	0.43	0.41	0.40	0.39	0.38	0.30	0.26	0.21	0.23	0.18	0.13	0.13
1.00	0.51	0.47	0.47	0.46	0.44	0.36	0.31	0.26	0.27	0.23	0.16	0.16
1.25	0.58	0.53	0.54	0.52	0.50	0.42	0.37	0.31	0.32	0.28	0.20	0.20
1.50	0.64	0.58	0.60	0.57	0.55	0.47	0.41	0.36	0.36	0.32	0.24	0.24
2.00	0.74	0.66	0.68	0.65	0.62	0.55	0.48	0.43	0.42	0.38	0.29	0.29
2.50	0.80	0.71	0.74	0.70	0.67	0.60	0.53	0.48	0.47	0.43	0.33	0.33
3.00	0.85	0.75	0.79	0.74	0.70	0.64	0.57	0.52	0.50	0.46	0.36	0.36
4.00	0.92	0.80	0.85	0.80	0.75	0.70	0.62	0.58	0.55	0.51	0.41	0.41
5.00	0.96	0.83	0.89	0.83	0.78	0.74	0.65	0.62	0.58	0.55	0.44	0.44

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	30328	26666	24785	24202	24785	26666	30328
50.0	30548	26644	24663	24053	24663	26644	30548
55.0	30701	26571	24498	23864	24498	26571	30701
60.0	30761	26419	24265	23609	24265	26419	30761
65.0	30763	26219	23991	23316	23991	26219	30763
70.0	30694	25957	23662	22969	23662	25957	30694
75.0	30645	25709	23345	22635	23345	25709	30645
80.0	30584	25443	23011	22285	23011	25443	30584
85.0	30571	25205	22700	21956	22700	25205	30571
90.0	30615	24997	22411	21648	22411	24997	30615

(cd/m²)

2021-05-13