


929001823604 1 x TLED InstantFit T5 HE 3ft 1400


1 x 1400 lm

Polar intensity diagram

Light output ratio 1.00
 Service upward 0.26
 Service downward 0.74


CIE flux code 35 63 84 74 100

UGRcen (4Hx8H, 0.25H) 26

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.40	0.38	0.38	0.37	0.36	0.29	0.26	0.22	0.24	0.20	0.17	
0.80	0.49	0.46	0.47	0.45	0.44	0.36	0.34	0.29	0.31	0.26	0.22	
1.00	0.57	0.53	0.54	0.52	0.51	0.43	0.39	0.34	0.36	0.32	0.26	
1.25	0.65	0.60	0.61	0.59	0.57	0.49	0.45	0.40	0.42	0.37	0.31	
1.50	0.71	0.64	0.67	0.64	0.62	0.54	0.50	0.45	0.46	0.42	0.35	
2.00	0.80	0.72	0.76	0.72	0.69	0.62	0.57	0.53	0.52	0.48	0.41	
2.50	0.87	0.77	0.82	0.77	0.73	0.67	0.62	0.58	0.57	0.53	0.46	
3.00	0.92	0.80	0.86	0.81	0.77	0.71	0.66	0.62	0.60	0.57	0.49	
4.00	0.98	0.85	0.92	0.86	0.81	0.77	0.71	0.67	0.65	0.62	0.53	
5.00	1.02	0.88	0.96	0.90	0.84	0.80	0.74	0.71	0.68	0.65	0.56	

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	9551	9534	9587	9775	10254	11330	13778
50.0	9290	9257	9260	9380	9759	10753	13409
55.0	9073	9016	8982	9011	9262	10105	12902
60.0	8896	8855	8749	8698	8773	9419	12353
65.0	8760	8698	8557	8428	8326	8657	11559
70.0	8678	8612	8438	8230	7943	7851	10551
75.0	8686	8545	8414	8127	7657	7047	9150
80.0	8743	8643	8462	8095	7462	6251	7113
85.0	8839	8738	8536	8134	7433	5661	4192
90.0	8982	8877	8703	8355	7590	5640	2428

(cd/m²)

2017-11-14