


929001823404 1 x TLED InstantFit T5 HE 2ft 1050


1 x 1050 lm

Polar intensity diagram

Light output ratio 1.00
 Service upward 0.26
 Service downward 0.74


CIE flux code 35 63 84 74 100

UGRcen (4Hx8H, 0.25H) 26

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.40	0.38	0.38	0.37	0.36	0.29	0.26	0.22	0.24	0.20	0.17	
0.80	0.49	0.46	0.47	0.45	0.44	0.36	0.34	0.29	0.31	0.26	0.22	
1.00	0.57	0.53	0.54	0.52	0.51	0.43	0.39	0.34	0.36	0.32	0.26	
1.25	0.65	0.60	0.61	0.59	0.57	0.49	0.45	0.40	0.42	0.37	0.31	
1.50	0.71	0.64	0.67	0.64	0.62	0.54	0.50	0.45	0.46	0.42	0.35	
2.00	0.80	0.72	0.76	0.72	0.69	0.62	0.57	0.53	0.52	0.48	0.41	
2.50	0.87	0.77	0.82	0.77	0.73	0.67	0.62	0.58	0.57	0.53	0.46	
3.00	0.92	0.80	0.86	0.81	0.77	0.71	0.66	0.62	0.60	0.57	0.49	
4.00	0.98	0.85	0.92	0.86	0.81	0.77	0.71	0.67	0.65	0.62	0.53	
5.00	1.02	0.88	0.96	0.90	0.84	0.80	0.74	0.71	0.68	0.65	0.56	

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	10746	10708	10756	10950	11470	12655	15339
50.0	10450	10394	10388	10503	10910	11989	14909
55.0	10210	10128	10076	10087	10341	11260	14317
60.0	10010	9945	9809	9726	9792	10477	13657
65.0	9851	9762	9595	9429	9288	9611	12724
70.0	9760	9665	9455	9195	8842	8707	11564
75.0	9767	9591	9418	9081	8520	7782	9961
80.0	9831	9698	9479	9035	8294	6886	7636
85.0	9942	9805	9552	9066	8243	6216	4327
90.0	10108	9964	9728	9304	8402	6144	1734

(cd/m²)

2017-11-14