


1 x TLED 31.5W 3000K 9290035778


1 x 3320 lm

Polar intensity diagram

Light output ratio 1.01
 Service upward 0.34
 Service downward 0.67


CIE flux code 32 59 82 66 101

UGRcen (4Hx8H, 0.25H) 25

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)															
	0.80				0.70				0.50				0.30			
	0.80	0.80	0.50	0.50	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.30	0.30	0.00	0.00
0.60	0.38	0.37	0.36	0.35	0.35	0.27			0.24	0.20	0.22	0.18	0.14			
0.80	0.48	0.45	0.45	0.44	0.42	0.35			0.31	0.26	0.28	0.24	0.18			
1.00	0.56	0.52	0.52	0.50	0.49	0.41			0.37	0.32	0.33	0.28	0.22			
1.25	0.63	0.58	0.59	0.57	0.55	0.47			0.42	0.37	0.38	0.33	0.26			
1.50	0.69	0.63	0.65	0.62	0.60	0.52			0.47	0.42	0.42	0.38	0.30			
2.00	0.79	0.70	0.73	0.70	0.67	0.60			0.54	0.49	0.48	0.44	0.35			
2.50	0.85	0.75	0.79	0.75	0.71	0.65			0.59	0.54	0.52	0.49	0.39			
3.00	0.90	0.79	0.84	0.79	0.75	0.69			0.62	0.58	0.55	0.52	0.42			
4.00	0.97	0.84	0.90	0.84	0.79	0.75			0.67	0.64	0.60	0.57	0.47			
5.00	1.01	0.87	0.94	0.87	0.82	0.78			0.70	0.67	0.63	0.60	0.49			

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	8462	8418	8670	8946	9577	10894	13057
50.0	8381	8312	8559	8767	9347	10694	13058
55.0	8353	8251	8486	8610	9117	10456	12997
60.0	8360	8233	8470	8494	8908	10169	12807
65.0	8431	8269	8500	8414	8717	9828	12466
70.0	8558	8365	8599	8396	8578	9432	11865
75.0	8738	8519	8770	8453	8520	8988	10867
80.0	8995	8753	9032	8620	8605	8567	9262
85.0	9328	9063	9386	8926	8919	8394	6868
90.0	9780	9487	9869	9431	9584	9137	5600

(cd/m²)

s22060022d

2022-07-11