



T5 26W 3000K 9290019088 1 x**1 x 3600 lm****Polar intensity diagram**

Light output ratio 1.00
 Service upward 0.24
 Service downward 0.76


CIE flux code 37 65 86 76 100

UGRcen (4Hx8H, 0.25H) 27

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)									
	0.80 0.80		0.70 0.70		0.70 0.70		0.50 0.50		0.30 0.30	
	0.50 0.50	0.30 0.10	0.50 0.50	0.30 0.10	0.50 0.50	0.30 0.10	0.30 0.10	0.10 0.10	0.30 0.10	0.00 0.00
0.60	0.41	0.39	0.39	0.38	0.37	0.30	0.28	0.23	0.26	0.22
0.80	0.50	0.47	0.48	0.47	0.45	0.38	0.35	0.30	0.32	0.28
1.00	0.58	0.54	0.55	0.54	0.52	0.44	0.41	0.36	0.38	0.34
1.25	0.66	0.61	0.63	0.60	0.58	0.51	0.47	0.42	0.43	0.39
1.50	0.72	0.66	0.69	0.66	0.63	0.56	0.52	0.47	0.48	0.44
2.00	0.82	0.73	0.77	0.73	0.70	0.64	0.59	0.54	0.54	0.51
2.50	0.88	0.78	0.83	0.79	0.75	0.69	0.64	0.60	0.59	0.56
3.00	0.93	0.81	0.88	0.83	0.78	0.73	0.68	0.64	0.62	0.59
4.00	0.99	0.86	0.94	0.88	0.83	0.78	0.72	0.69	0.67	0.64
5.00	1.04	0.89	0.97	0.91	0.85	0.82	0.76	0.73	0.70	0.67

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	16383	15919	15985	16614	17930	20198	23951
50.0	15922	15326	15277	15804	17044	19315	23334
55.0	15524	14783	14603	15003	16128	18345	22590
60.0	15204	14298	13963	14205	15164	17248	21635
65.0	14954	13864	13354	13406	14147	16004	20411
70.0	14785	13488	12778	12605	13063	14559	18750
75.0	14697	13175	12246	11818	11931	12908	16474
80.0	14713	12956	11801	11103	10827	11119	13272
85.0	14848	12877	11530	10611	10002	9606	9010
90.0	15132	13049	11649	10720	10157	9975	17531

(cd/m²)

2018-03-26