



T5 26W 4000K 9290019089 1 x**1 x 3900 lm****Polar intensity diagram**

Light output ratio 1.00
 Service upward 0.24
 Service downward 0.76


CIE flux code 37 65 86 76 100

UGRcen (4Hx8H, 0.25H) 27

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.10	0.00
0.60	0.80	0.80	0.70	0.70	0.70	0.70	0.35	0.30	0.32	0.28	0.24	0.00
0.80	0.50	0.50	0.50	0.50	0.50	0.30	0.30	0.30	0.30	0.30	0.30	0.00
1.00	0.58	0.54	0.55	0.54	0.52	0.44	0.41	0.36	0.38	0.34	0.28	0.00
1.25	0.66	0.61	0.63	0.60	0.58	0.51	0.47	0.42	0.43	0.39	0.33	0.00
1.50	0.72	0.66	0.69	0.66	0.63	0.56	0.52	0.47	0.48	0.44	0.37	0.00
2.00	0.82	0.73	0.77	0.73	0.70	0.64	0.59	0.54	0.54	0.51	0.44	0.00
2.50	0.88	0.78	0.83	0.79	0.75	0.69	0.64	0.60	0.59	0.56	0.48	0.00
3.00	0.93	0.81	0.88	0.83	0.78	0.73	0.68	0.64	0.62	0.59	0.52	0.00
4.00	0.99	0.86	0.94	0.88	0.83	0.78	0.72	0.69	0.67	0.64	0.56	0.00
5.00	1.04	0.89	0.97	0.91	0.85	0.82	0.76	0.73	0.70	0.67	0.59	0.00

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	17749	17246	17317	17998	19424	21881	25947
50.0	17248	16603	16550	17121	18464	20924	25279
55.0	16818	16015	15820	16253	17471	19874	24472
60.0	16471	15489	15127	15388	16427	18685	23437
65.0	16200	15019	14467	14523	15326	17337	22112
70.0	16017	14612	13843	13655	14151	15772	20312
75.0	15921	14273	13267	12803	12925	13983	17847
80.0	15939	14036	12784	12029	11730	12046	14378
85.0	16085	13950	12491	11495	10835	10407	9761
90.0	16393	14137	12620	11613	11004	10806	18981

(cd/m²)

2018-03-26