


1 x TLED 26W 3000K 9290023520

1 x 3700 lm

Polar intensity diagram




Light output ratio 1.00
Service upward 0.27
Service downward 0.73

CIE flux code 36 64 85 73 100

UGRcen (4Hx8H, 0.25H) 28

Quantity estimation diagram




Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80 0.80				0.70 0.70 0.70 0.70				0.50 0.50 0.30 0.30			
	0.80	0.80	0.50	0.50	0.50	0.50	0.30	0.30	0.30	0.30	0.10	0.00
0.60	0.40	0.38	0.38	0.37	0.36	0.29	0.27	0.22	0.25	0.21	0.17	
0.80	0.50	0.47	0.47	0.46	0.44	0.37	0.34	0.29	0.31	0.27	0.22	
1.00	0.58	0.53	0.54	0.53	0.51	0.43	0.40	0.35	0.36	0.32	0.27	
1.25	0.65	0.60	0.62	0.59	0.57	0.50	0.46	0.41	0.42	0.38	0.31	
1.50	0.72	0.65	0.67	0.65	0.62	0.55	0.50	0.45	0.46	0.42	0.35	
2.00	0.81	0.72	0.76	0.72	0.69	0.63	0.57	0.53	0.52	0.49	0.41	
2.50	0.87	0.77	0.82	0.78	0.74	0.68	0.62	0.58	0.57	0.54	0.46	
3.00	0.92	0.81	0.86	0.81	0.77	0.72	0.66	0.62	0.60	0.57	0.49	
4.00	0.98	0.85	0.92	0.86	0.81	0.77	0.71	0.67	0.65	0.62	0.53	
5.00	1.02	0.88	0.96	0.90	0.84	0.80	0.74	0.71	0.68	0.65	0.56	

Ceiling mounted

UGR diagram



Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	22237	22155	22099	22333	23242	25696	31351
50.0	21495	21355	21190	21253	21898	24093	30215
55.0	20840	20673	20391	20243	20542	22362	28841
60.0	20314	20107	19753	19385	19277	20579	27356
65.0	19880	19698	19207	18635	18110	18673	25416
70.0	19588	19416	18841	18084	17155	16729	23112
75.0	19511	19334	18706	17843	16441	14806	20132
80.0	19582	19373	18805	17794	16040	12957	15671
85.0	19736	19446	18957	18033	15992	11720	9316
90.0	20060	19785	19264	18378	16557	11924	11000

(cd/m²)

2020-05-28